DATA SHEET 0034006

valid from: **UNITRONIC® 100 CY** 01.01.2019



Application

UNITRONIC® 100 CY is a screened control and signal cable with small cross-sections for fixed installation as well as occasional flexing at free, non-continuously recurring movement without tensile load. It is used in dry, damp and wet interiors but it is not appropriate for outside

The cables are used in the milliampere range for computer systems, electronic control equipment, office machines, balances etc. and wherever the thinnest possible control cables are required.

Design

Stranding

Outer sheath

Design Design based on standard VDE 0812 Conductor fine wire strands of bare copper wires

Insulation special PVC-based compound

Core identification code according to UNITRONIC® colour code

cores are stranded in layers Inner sheath special PVC-based compound colour: grey (similar RAL 7001) Screen Braiding with tinned copper wires

> special PVC-based compound colour: grey (similar RAL 7001)

Electrical properties at 20°C

Specific volume resistivity > 20 G Ω x cm

C/C: approx. 120 nF/km Mutual capacitance

C/S: approx. 160 nF/km

(at 800 Hz)

Inductance approx. 0.65 mH/km

0.14 mm²: 350 V (not for power applications) Peak operating voltage

≥ 0.25 mm²: 500 V (not for power applications)

Test voltage 0.14 mm²: 1200 V

≥ 0.25 mm²: 1500 V

Mechanical and thermal properties

Minimum bending radius Flexing: 20 x cable Ø

Fixed installation: 6 x cable Ø

Flexing: - 5°C up to +70°C Temperature range

> Fixed installation: - 40 °C up to +80 °C flame retardant acc. to IEC 60332-1-2

Flammability General requirements This cable is conform to the EU-Directive 2011/65/EU

(RoHS, Restriction of the use of certain hazardous substances).