


| | | |
|---------------------------|--|--|
| 0167001 | DATA SHEET |  |
| Valid from: 01.04.2019 | IEC compensating cable KPL Y XX x 1,5 | |

Application

The compensating cables KPL Version Y XX x 1,5 mm² are multi-cored, PVC insulated cables which transmit the thermoelectric voltage of PtRh/Pt thermocouples. They are for flexible use and fixed installation in dry and damp rooms with medium mechanical load. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range.

Design

| | | |
|---------------------|--|--------------------|
| Conductor | 1.5 mm ² (48 x 0.20 mm) | |
| Conductor material | RCB/SCB alloying, accuracy class 2 according IEC 60584 | |
| | Positive conductor: | Cu (copper) |
| | Negative conductor: | CuNi (cupronickel) |
| Core insulation | PVC compound | |
| Core identification | Positive conductor: | orange |
| | Negative conductor: | white |
| Core layering | Cores twisted together | |
| Outer sheath | PVC compound, colour: | orange |

Electrical properties

| | |
|----------------------------|---|
| Limiting deviation class 2 | ±60 µV (±5.0 °C) / measuring point temperature +1000 °C |
|----------------------------|---|

Mechanical and thermal properties

| | | |
|------------------------|---|---------------------|
| Temperature range | fixed installed: | -40 °C up to +80 °C |
| | occasional flexing: | -5 °C up to +70 °C |
| Minimum bending radius | occasional flexing: | 12 x cable diameter |
| Flammability | flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2 | |

| | | |
|---|--------------------------------------|-------------|
| Creator: TOME/PCM Released: ALTE/PDC | Document: DB0167001EN Version: 02 | Page 1 of 1 |
|---|--------------------------------------|-------------|