


<b>2170296</b>	<b>DATA SHEET</b>	
<b>valid from: 27.10.2020</b>	<b>ETHERLINE® H Cat.5e 4x2x24/1 AWG</b>	


### Application

Field of use: Installation cable for generic cabling systems acc. to ISO/IEC 11801 and EN 50173

Performance: Bandwidth up to 100 MHz acc. to IEC 61156-5 Category 5e and EN 50288-2-1

Characteristics: halogen free, flame retardant, and largely resistant to acids, alkalis and certain oils

Applications: Profinet with 4 pairs, EtherCAT, EtherNet/IP, Power over Ethernet (IEEE 802.3af), Power over Ethernet Plus (IEEE 802.3at) and many others




### Design

Certification	certified for CC-Link IE Field Network
Conductor	solid bare copper 24/1 AWG
Insulation	foamed PE core $\varnothing$ : ca. 1,00 mm
Core identification code	pair 1: white-blue/blue; pair 2: white-orange/orange; pair 3: white-green/green; pair 4: white-brown/brown
Stranding	cores twisted to pairs, pairs stranded together
Screen	plastic laminated aluminum foil on top: braid of tinned copper wire (coverage ca. 85 %)
Outer sheath	LSZH blue, similar RAL 5021 outer $\varnothing$ : ca. 6.1 mm

### Electrical properties at 20°C

Loop resistance	max. 19.0 $\Omega$ /100 m
Insulation resistance	min. 5 G $\Omega$ xkm
Mutual capacitance	nom. 48 nF/km
Characteristic impedance	nom. 100 $\Omega$ acc. to IEC 61156-6
Velocity of propagation	0.77 c
Signal propagation time	$\leq$ 430 ns/100 m
Delay skew	$\leq$ 25 ns/100 m (at 100 MHz)
Operating voltage (max.)	125 V (not for power purposes)
Test voltage	core/core: 1000 V core/screen: 1000 V

Creator: KIOS / PDC	Document: DB2170296EN	Page 1 of 2
Released: ALTE / PDC	Version: 06	

<b>2170296</b>	<b>DATA SHEET</b>	
<b>valid from: 27.10.2020</b>	<b>ETHERLINE® H Cat.5e 4x2x24/1 AWG</b>	

### Electrical transmission properties at 20°C

The transmission characteristics meet the requirements of the standards EN 50288-2-1 and IEC 61156-5 for category 5e. The normative requirements for the transmission properties are shown in the following table:

f [MHz]		4	10	16	20	31,25	62,5	100
(max.) Attenuation	[dB/100 m]	4	6,3	8	9	11,4	16,5	21,3
(min.) TCL	[dB]	34	30	28	27	25,1	22	20
(min.) EL TCTL	[dB/100 m]	23	15	10,9	9	5,1	—	—
(min.) NEXT	[dB]	56,3	50,3	47,2	45,8	42,9	38,4	35,3
(min.) PS EL FEXT	[dB/100 m]	49	41	36,9	35	31,1	25,1	21
(min.) ACR-F/EL FEXT	[dB/100 m]	52	44	39,9	38	34,1	28,1	24
(min.) Return Loss	[dB]	23	25	25	25	23,6	21,5	20,1

### Mechanical and thermal properties

Minimum bending radius	fixed: 7.5 x cable Ø
Temperature range	fixed: -30 °C bis +80 °C
Flammability	flame retardant acc. to IEC 60332-1-2 resp. EN 60332-1-2
Halogen free	acc. to IEC 60754-1 resp. EN 60754-1
Corrosivity of gases	acc. to IEC 60754-2 resp. EN 60754-2
General requirements	This cable is conform to EU-Directive 2014/35/EU (Low Voltage Directive) and to EU-Directive 2011/65/EU (RoHS, Restriction of the use of certain hazardous substances).
Environmental information	These cables meet the substance-specific requirements of the EU Directive 2011/65/EU (RoHS).

Creator: KIOS / PDC	Document: DB2170296EN	Page 2 of 2
Released: ALTE / PDC	Version: 06	