DATA SHEET

valid from: 2021-03-03

1026513

ÖLFLEX® CHAIN 90 P



Application

ÖLFLEX® CHAIN 90 P are highly-flexible PUR single core cables approved for the European, North American and Canadian market, for permanent flexible use in power chains and fixed installation with narrow bending radii under increased mechanical load conditions. They are also suitable for use in dry, damp or wet areas. These products are suitable for outdoor use if the indicated temperature range is observed. ÖLFLEX® CHAIN 90 P are increased resistant to oils and at room temperature largely resistant to acids and alkalis.

The outer sheath withstands high mechanical stresses, in particular abrasion and dragging. It is also cut proof and resists microbes and hydrolysis.

ÖLFLEX® CHAIN 90 P are especially suitable for increased requirements (Extended Line) in power chains and in permanently moved machine parts. They are suitable for linear, automated movements. The maximum tensile load is 15 N/mm2 of conductor cross-section during installation and operation. Compulsory guidance is not permitted.

Application range:

Power chains or moving machine parts, for wiring of electric and electronic equipment in switch cabinets, test systems in the automotive industry, vehicles and stationary fuel cell systems

PUR sheathed cables for external wiring USE acc. to RU:

USE acc. to cRU: Cables for internal or external interconnection with or without mechanical use.

Design

Design acc. to UL AWM Style 11624, CSA C22.2 No. 210-15

and based on EN 50525-1

Certification RU AWM 758, Style 11624 (File No. E63634)

> cRU AWM I A/B, II A/B (File No. E63634) DNV (Certificate no. TAE000047C)

Conductor extra fine wire strands of bare copper acc. to IEC 60228 resp. EN 60228, Class 6

Insulation Special compound based on TPE

Core identification code Black or GN/YE

Outer sheath TMPU Polyurethane compound (UL/CSA 80° C rating)

colour: Black, similar RAL 9005

Electrical properties at 20 °C

Nominal voltage IEC U₀ /U: 600 / 1000 V

RU/cRU: 1000 V Rated voltage Test voltage 4000 V AC

Mechanical and thermal properties

Minimum bending radius flexing: up from 7.5 x outer diameter

fixed installation: 3 x outer diameter

flexing (EN): Temperature range -35 °C up to +80 °C max. conductor temp.

flexing (RU/cRU): up to +80 °C max. conductor temp. fixed installation (EN): -50 °C up to +80 °C max. conductor temp. fixed installation(RU/cRU): up to +80 °C max. conductor temp.

Bending cycles and power chain

See Selection Table A2-1 in the appendix of our online catalogue

operation parameters For use in power chains: Please comply with assembly guideline Appendix T3

TW-0 (5000 cycles at $\geq +5$ °C) Torsional stress

TW-2 (2000 cycles at ≥ -40°C) ± 150°/m at 1 rotation per minute

Flammability flame retardant acc. to:

IEC 60332-1-2 resp. EN 60332-1-2 IEC 60332-3-24 resp. EN 60332-3-24 IEC 60332-3-25 resp. EN 60332-3-25

RU: Vertical flame test VW-1

cRU: FT1

Halogen free acc. to VDE 0472-815 acc. to EN 50618 UV resistance

FN 50620

EN ISO 4892-2-2013, method A (change of colour allowed)

Ozone resistance acc. to EN 50396, method B

Document: DB1026513EN Creator: PESA / PDC Page 1 of 2 ALTE / PDC Version: 05 Released:

Oil resistance acc. to EN 50363-10-2

Tests acc. to IEC 60811 resp. EN 60811, EN 50395, EN 50396

UL 1581 und CSA C22.2

General requirements

These cables are conform to the EU-Directives 2014/35/EU (Low Voltage Directive)

Environmental information These cables meet the substance-specific requirements of the EU Directive 2011/65/EU (RoHS).

Creator: PESA / PDC Document: DB1026513EN

Released: ALTE / PDC Version: 05

Page 2 of 2