


2170297	DATA SHEET	
valid from: 23.03.2020	ETHERLINE® P Cat. 5e 4x2x24/1 AWG	

Application

Field of use:	Installation cable for generic cabling systems acc. to ISO/IEC 11801 and EN 50173
Performance:	Bandwidth up to 100 MHz acc. To IEC 61156-5 Category 5e and EN 50288 2-1
Characteristics:	halogen free, flame retardant, oil resistant, UV resistant and largely resistant to acids, alkalis and certain oils
Applications:	Profinet with 4 pairs, EtherCAT, EtherNet/IP, Power over Ethernet (IEEE 802.3af), Power over Ethernet Plus (IEEE 802.3at) and many others



Design

Certification	UL AWM style 11117 and 21576 (1000 V, 80 °C) acc. to UL 758 cRU AWM I/II A/B (FT2) acc. to CSA C22.2 No.210 certified for CC-Link IE Field Network
Conductor	solid bare copper 24/1 AWG
Insulation	foamed PE core Ø: ca. 1,00 mm
Core identification code	pair 1: white-blue/blue; pair 2: white-orange/orange; pair 3: white-green/green; pair 4: white-brown/brown
Stranding	cores twisted to pairs, pairs stranded together wrapped by plastic tape
Screen	plastic laminated aluminum foil on top: braid of tinned copper wire (coverage ca. 85 %)
Outer sheath	PUR blue, similar to RAL 5021 outer Ø: ca. 6.1 mm

Electrical properties at 20°C

Loop resistance	max. 19,2 Ω/100 m
Insulation resistance	min. 5 GΩxkm
Mutual capacitance	nom. 48 nF/km
Characteristic impedance	nom. 100 Ω acc. to IEC 61156-6
Velocity of propagation	0.77 c
Signal propagation time	<433 ns/100 m
Peak operating voltage	VDE: 125 V (not for power purposes) UL: 1000 V
Test voltage	core/core: 3000 V core/screen: 3000 V

Creator: KIOS / PDC	Document: DB2170297EN	Page 1 of 2
Released: ALTE / PDC	Version: 08	

2170297	DATA SHEET	
valid from: 23.03.2020	ETHERLINE® P Cat. 5e 4x2x24/1 AWG	

Electrical transmission properties at 20°C

The transmission characteristics meet the requirements of the standards EN 50288-2-1 and IEC 61156-5 for category 5e.
The normative requirements for the transmission properties are shown in the following table:

f [MHz]	4	10	16	20	31,25	62,5	100
(max.) Attenuation [dB/100 m]	4	6,3	8	9	11,4	16,5	21,3
(min.) TCL [dB]	34	30	28	27	25,1	22	20
(min.) EL TCTL [dB/100 m]	23	15	10,9	9	5,1	—	—
(min.) NEXT [dB]	56,3	50,3	47,2	45,8	42,9	38,4	35,3
(min.) PS EL FEXT [dB/100 m]	49	41	36,9	35	31,1	25,1	21
(min.) ACR-F/EL FEXT [dB/100 m]	52	44	39,9	38	34,1	28,1	24
(min.) Return Loss [dB]	23	25	25	25	23,6	21,5	20,1

Mechanical and thermal properties

Minimum bending radius	fixed:	7.5 x cable Ø
Temperature range	fixed:	-30 °C up to +80 °C
	occasional flexing:	-5 °C up to +50 °C
	UL:	80 °C
Flammability	flame retardant acc. to IEC 60332-1-2 resp. EN 60332-1-2	
	Horizontal flame acc. to UL 1581 §1090 and §1100	
Halogen free	acc. to VDE 0472-815	
UV resistance	acc. to. ISO 4892-2, method A	
Oil resistance	acc. to. EN 50363-10-2	
General requirements	These cables are conform to the EU-Directive 2011/65/EU (RoHS, Restriction of the use of certain hazardous substances) and the LV-Directive 2014/35/EU (Low voltage Directive).	
Environmental information	These cables meet the substance-specific requirements of the EU Directive 2011/65/EU (RoHS).	

Creator: KIOS / PDC	Document: DB2170297EN	Page 2 of 2
Released: ALTE / PDC	Version: 08	