## DATA SHEET 1028752

valid from: ÖLFLEX® FD 891 P 22.08.2022



## **Application**

ÖLFLEX® FD 891 P cables are high-flexible, oil-resistant cables for power chains with an outer sheath of Polyurethane for the European, North American and Canadian market.

They are designed for flexible use as well as for fixed installation subject to medium mechanical load conditions.

They are among others designed for use in dry, damp and wet areas.

They are suitable for outdoor use if the indicated temperature range is observed.

ÖLFLEX® FD 891 P cables are increased resistant to oils and at room temperature largely resistant to acids and alkalis.

The outer sheath withstands high mechanical stresses, in particular abrasion and dragging. It is also cut proof and resists microbes and hydrolysis.

They are suitable for linear, automated movements. The maximum tensile load is 15 N/mm<sup>2</sup> of conductor cross-section during installation and operation. Compulsory guidance is not permitted.

Application range: power chains or moving machine parts, machine tools and transfer lines, suitable for use in measuring, control and regulating circuits, plant engineering

USE according to UL: PUR sheathed cables for external interconnection of electronic equipment USE according to cRU: Cables for internal and external interconnection with or without mechanical use

Design

Design acc. to UL AWM Style 20234, CSA C22.2 No. 210-15 and

based on EN 50525-2-21

Certification UL AWM 758, Style 20234 (File No. E63634)

cRUus AWM I A/B, II A/B (File No. E63634)

Conductor extra fine wire strands of bare copper acc. to IEC 60228 resp. EN 60228, class 6

Insulation PVC compound (UL/CSA 80°C rating)

acc. to VDE 0293-1, with or without GN/YE ground conductor Core identification code

black cores with white numbers acc. to EN 50334

Outer sheath TPU compound (UL/CSA 80°C rating)

resp. TPU based on EN 50363-10-2 colour: black, similar RAL 9005

Electrical properties at 20 °C

Nominal voltage IEC U<sub>0</sub> /U: 300 / 500 V

UL / CSA: 600 V

Test voltage core / core: 4000 V AC

Mechanical and thermal properties

Minimum bending radius flexing: up from 7.5 x outer diameter

fixed installation: 4 x outer diameter

flexing (IEC): -5 °C up to +70 °C max. conductor temperature Temperature range

flexing (UL/CSA): -5 °C up to +80 °C max. conductor temperature fixed installation (IEC): -40 °C up to +80 °C max. conductor temperature fixed installation (UL/CSA): up to +80 °C max. conductor temperature

Bending cycles and power chain

See Selection Table A2-1 in the appendix of our online catalogue operation parameters

For use in power chains: Please comply with assembly guideline Appendix T3

flame retardant acc. to IEC 60332-1-2 resp. EN 60332-1-2 Flammability

UL: vertical flame test VW-1

CSA: FT1

UV resistance acc. to EN 50525-1 cables with black sheath are suitable

for permanent outdoor use.

acc. to EN 50618 acc. to EN 50620

acc. to EN ISO 4892-2-2013, method A (change of colour allowed)

Oil resistance acc. to EN 50363-10-2

Tests acc. to IEC 60811 resp. EN 60811, EN 50395, EN 50396

UL 1581 und CSA C22.2

Document: DB1028752EN Creator: LABU / PDC Page 1 of 2 ALTE / PDC Version: Released:

1028752	DATA SHEET	& LADD
valid from: 22.08.2022	ÖLFLEX® FD 891 P	<b>WLAPP</b>

**General requirements**These cables are conform to the EU-Directive 2014/35/EU (Low Voltage Directive).

A part of these cables (see www.lappkabel.com/cpr) are classified in accordance with the EU-Regulation no. 305/2011 (CPR).

**Environmental information** These cables meet the substance-specific requirements of the EU Directive 2011/65/EU (RoHS).

Creator: LABU / PDC Document: DB1028752EN
Released: ALTE / PDC Version: 06
Page 2 of 2