


21700540	DATA SHEET	
Valid from: 17.09.2018	Field-Terminable Connector RJ45 Cat.5e FM45	

Description

- Tool-free switchable, field-terminable RJ45-connector
- IDC-contacting, Cat.5e
- Can be re-switched, tension-resistant and vibration-resistant
- For screened as well as unscreened cables up to 8 mm diameter



General characteristics

Pol number	8
Type of connection	IDC-crimping technology
Temperature range (operation)	-20 °C to 70 °C (-4 °F to 158 °F)

Mechanical characteristics

Degree of soiling	2
Cable strain relief	>50 N
Housing, colour	Grey, similar RAL 7042
Allowable wire Ø	0,4 mm to 0,54 mm (AWG 26 - AWG 23) conditional 0,64 mm (AWG 22)
Allowable strand Ø	0,12 mm ² to 0,32 mm ² (AWG 26/7 - AWG 22/7)
Outer sheath Ø	4,5 mm to 8,0 mm


Electrical characteristics

Rated current I _N	1,75 A
------------------------------	--------


Standard

Connectors for electronic equipment – part 7	IEC 60603-7
Connectors for electronic equipment – part 7-3	IEC 60603-7-3
Information technology – generic cabling for customer premises	ISO/IEC 11801

Creator: MOKO2/PDP Released: IVSE1/PDP	Document: DB21700540EN Version: 02	Page 1 of 2
---	---------------------------------------	-------------

21700540	DATA SHEET	
Valid from: 17.09.2018	Field-Terminable Connector RJ45 Cat.5e FM45	

Technical drawing



Application range

Automation, industrial machinery and plant engineering

Note

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MOKO2/PDP Released: IVSE1/PDP	Document: DB21700540EN Version: 02	Page 2 of 2
---	---------------------------------------	-------------