
2170842 DATA SHEET Valid from: 28.05.2018 UNITRONIC® BUS ASI (PVC) A



Description

UNITRONIC® BUS ASI PVC A is a two-core and flat actuator/sensor bus cable with increased fire resistance and UL approvals for the AS-INTERFACE (actuator-sensor-interface) networking system for the lower field area. The cable is particularly suitable for applications with high mechanical stress which require a high oil resistance. It is suitable for fixed installation and flexible applications and is flame retardant. Data transmission for AS-INTERFACE telegrams and power supply for AS-I slaves, master, repeater, extender and sensors is done via this unscreened, geometrically-coded two-core flat cable. The contacting of the conductors by the insulationdisplacementsystem of the AS-I modules is possible without stripping the insulation. The cable is designed for indoor applications.



Approvals

c(UL)us Type CMG 90°C acc. to UL 444
(UL) PLTC/CL2 acc. to UL 13

c(RU)us UL AWM style 2095 acc. to UL 758

Variations

 Part-Nr.
 Colour

 2170842
 Yellow, similar RAL 1012

 2170843
 Black, similar RAL 9005

 2170844
 Red, similar RAL 3000

General characteristics

Core identification code

Conductor Extra-fine-stranded, tinned copper wires,

Conductor Ø approx. 1.5 mm

Insulation PVC-compound

Core Ø approx. 2.5 mm Brown(+) and Blue(-)

Stranding 2 cores parallel deviation

brown core assembled in line with leading edge

Outer sheath PVC compound

Colour in accordance with variations and part number

outer $\ensuremath{\text{\emptyset}}$ and dimensions in accordance with ASI specification

DATA SHEET

Valid from: 28.05.2018

2170842

UNITRONIC® BUS ASI (PVC) A



Mechanical characteristics

Minimum bending radius power chain horizontal 75 mm (on broadside) power chain vertical 50 mm

multiple bendings \geq 24 mm single \geq 12 mm

Permissible temperature range fixed installation -30 °C up to +90 °C

at installation -20 °C up to +90 °C

Flame propagation flame retardant acc. to IEC 60332-1-2

flame retardant acc. to UL 1581 Sec. 1090 (Horizontal Cable Flame)

flame retardant acc. to UL 1581 Sec. 1100 (FT-2) flame retardant acc. to UL 1685 (CSA FT 4) $\,$

Oil resistance acc. to UL 1581, Sec. 480 (60 °C)

Electrical characteristics

Resistance max. 13.7 Ω/km Insulation resistance min. 1 M Ω x km

Mutual capacitance nom. 80 nF/km at 800 Hz

Operating peak voltage 300 V (not for power purposes)
Test voltage core/core: 2000 V

Standard

EU-Directive Dangerous and forbidden substances acc. to RoHS

directive (2011/65/EU) are not allowed to the

manufacturing.