DATA SHEET

Valid from: 17.09.2018

21700547

ED-PB-90-LED-FC



PROFIBUS bus connector, Sub-D with Fast Connect, cable outlet 90°, integrated terminating resistor, with LED diagnosis, with 12 Mbit/s

Approvals







Technical data

Cable outlet: 90°

Connection type: Fast Connect

Programming-/Diagnosis-interface: No

For cable type: Solid conductor (versions with "S" at the cover)

Solid conductor/7-/19-wires (version from 01.07.2015, identifiable

with the missing "S")

For outer cable diameter: 5.0 to 8.0 mm

Degree of protection: IP20 Pollution degree: 2

Dimensions: 72 x 40 x 17 mm (LxWxH)

Terminating resistor: 150Ω , integrated, connectable via slide switch Interfaces: PROFIBUS- participant: Sub-D socket, 9-pins PROFIBUS-cable: FC standard cable, \emptyset 0.64 mm

Transmission rate: Max. 12 Mbit/s

Supply voltage: 4.75 to 5.25 V DC (from terminal)

Current consumption: Max. 12.5 mA Operating temperature: -25 °C to +70 °C

*The maximum ambient temperature for UL is + 60 °C

Transport- and storage temperature: - 25 °C to + 80 °C
Relative humidity: Max. 75 % at + 25 °C
Material, housing: Metallized housing

Fixture screw: 4-40 UNC
Norms/approvals: IEC 61158
IEC 61784

UL-File E331560 EC001132

ETIM 5.0 Class-ID: EC001132
LED diagnosis: Bus operation (green)

Participant sending (blue)


Terminating resistor switched ON (orange)

Creator: PAMA7 Document: DB21700547EN Page 1 of 2

21700547	DATA SHEET	& LAPP
Valid from: 17.09.2018	ED-PB-90-LED-FC	

Description

When used in the middle of a PROFIBUS network (two cable connections, node) the switch at the connector must be in the 'OFF' position. If used as a terminating connector (one cable connection, segment end), the switch must be in the 'ON' position. If the switch is in the 'ON' position the outbound bus cable is disconnected.



Application range

Automation, industrial machinery and plant engineering

Note

Photographs are not true to scale and do not represent detailed images of the respective products.

Creator: PAMA7	Document: DB21700547EN	Page 2 of 2
Released: IVSE1/PDP	Version: 03	