


<b>2170466</b>	<b>DATA SHEET</b>	
<b>valid from: 09.08.2021</b>	<b>ETHERLINE® H Cat. 6A 4x2x22/1 AWG</b>	


### Application

Field of use: Installation cable for cabling systems acc. to ISO/IEC 11801 and EN 50173. Meeting the transmission requirements of IEC 61156-5, Category 6A and EN 50288-10-1. Compliant to the "PROFINET Cabling and Interconnection Technology" guideline.

Performance: 4-pair, screened foiled twisted pair cable (S/FTP), having a nominal impedance of 100 Ω, supporting a bandwidth of 10 Gbit/s (e.g. 100BASE-T, 1000BASE-T, 2.5GBASE-T, 5GBASE-T, 10GBASE-T) over up to 100 m.

Characteristics: Flame retardant, no flame propagation, halogen free

Applications: PROFINET, EtherCAT, EtherNet/IP, PoE (IEEE 802.3af), PoE+ (IEEE 802.3at), PPOE (IEEE 802.3bt) and others



### Design

Certification EN 13501-6 and EN 50575 Classification of fire behaviour

Conductor solid bare copper  
22/1 AWG

Insulation polyolefin (foamed)  
core diameter: nom. 1.50 mm

Core identification code pair 1: white/blue, pair 2: white/orange, pair 3: white/green, pair 4: white/brown  
(colored ring marking on the white cores is optional)

Stranding 2 cores stranded to pair,  
4 pairs stranded to bundle

Pair screen plastic laminated aluminium foil (overlapping)


Screen braid of tinned copper wires (coverage 85 % ± 5 %)

Outer sheath FRNC  
green, similar RAL 6018  
outer diameter: 8.70 mm (± 0.3 mm)

### Electrical properties at 20 °C

Loop resistance	≤ 12.2 Ω/100 m	
Insulation resistance	≥ 5 GΩ×km	
Mutual capacitance	800 Hz:	42 nF/100 m
Coupling attenuation	30 MHz - 100 MHz:	≥ 80 dB
	100 MHz - 500 MHz:	≥ 80 - 20×log <sub>10</sub> (f / 100)
Characteristic impedance	100 MHz:	100 Ω acc. to IEC 61156-5
Velocity of propagation	100 MHz:	0.80 c
Signal propagation time	4 MHz - 500 MHz:	≤ 480 ns/100 m
Delay skew	4 MHz - 500 MHz:	≤ 20 ns/100 m
Maximum operating voltage	EN:	100 V (not for power applications)
Test voltage	core/core:	700 V
	core/screen:	700 V

Creator: KIOS / PDC	Document: DB2170466EN	Page 1 of 2
Released: ALTE / PDC	Version: 04	

<b>2170466</b>	<b>DATA SHEET</b>	
<b>valid from: 09.08.2021</b>	<b>ETHERLINE® H Cat. 6A 4x2x22/1 AWG</b>	

### Electrical transmission properties at 20°C

The transmission characteristics meet the requirements of the standards EN 50288-10-1 and IEC 61156-5 for category 6A. The normative requirements for the transmission properties are shown in the following table:

f [MHz]		4	10	20	62,5	100	200	250	500
(max.) Attenuation	[dB/100 m]	3,8	5,9	8,4	15	19,1	27,6	31,1	45,3
(min.) TCL	[dB]	34	30	27	22	20	17	16	—
(min.) EL TCTL	[dB/100 m]	23	15	9	—	—	—	—	—
(min.) NEXT	[dB]	66,3	60,3	55,8	48,4	45,3	40,8	39,3	34,8
(min.) PS EL FEXT	[dB/100 m]	53	45	39	29,1	25	19	17	11
(min.) ACR-F/EL FEXT	[dB/100 m]	56	48	42	32,1	28	22	20	17
(min.) Return Loss	[dB]	23	25	25	21,5	20,1	18	17,3	17,3

### Mechanical and thermal properties

Minimum bending radius	fixed installation:	10 × outer diameter
Temperature range	fixed installation:	-25 °C up to +80 °C
Flammability	flame retardant acc. to IEC 60332-1-2 resp. EN 60332-1-2	no flame propagation acc. to IEC 60332-3-25 resp. EN 60332-3-25
Halogen free	acc. to IEC 60754-1 resp. EN 60754-1	
Corrosivity of gases	acc. to IEC 60754-2 resp. EN 60754-2	
Smoke density	acc. to IEC 61034-2 resp. EN 61034-2	

### General requirements

This cable is conform to the EU-Directive 2011/65/EU (RoHS, Restriction of the use of certain hazardous substances) and the LV-Directive 2014/35/EU (Low voltage Directive). This cable is classified in accordance with the EU-Regulation no. 305/2011 (CPR).

### Environmental information

These cables meet the substance-specific requirements of the EU Directive 2011/65/EU (RoHS).

Creator: KIOS / PDC	Document: DB2170466EN	Page 2 of 2
Released: ALTE / PDC	Version: 04	