


29021902	DATA SHEET
Valid from: 01.12.2020	GOF DUPLEX Patchcord ST/SC E9 OS2, 2m

Description

- GOF Optical fiber Patchcord
- 2x ST-Simplex-plug on straight SC-Duplex-plug



General characteristics

Connection method, connector	2x ST-Simplex (ST-S), metal SC-Duplex (SC-D), blue
Polishing	PC (physical contact)
Fiber type	Singlemode E9 OS2
Number of lead	2
Temperature range	-25°C to +70°C (-13°F to 158°F) (Operation) -25°C to +70°C (-13°F to 158°F) (Storage) -10°C to +60°C (14°F to 140°F) (Installation)

Additional note

Standard length 2m. Data sheet also valid for variant lengths.

Optical properties

Insertion loss (max.)	0.25 dB / 0.5 dB (mean/ 97%)
Return loss (min.)	45 dB

Mechanical properties


Plug

Housing, material	SC: PBT ST: Hpb59-1
Ferrule, material	Zirconia
Ferrule-Ø	2.5 mm
Boot, material	TPE, black and blue
Tensile strength	100 N
Mating cycles (min.)	1000

Line

Outer coating, material	LSOH, yellow
Cable outer diameter	2 mm
Min bending radius	50 mm (Installation) 25 mm (Operation)

Technical drawing



29021902	DATA SHEET
Valid from: 01.12.2020	GOF DUPLEX Patchcord ST/SC E9 OS2, 2m

Standards / Approvals

Fibre optic connector interfaces - Type SC	IEC 61754-4
Fibre optic connector interfaces - Type BFOC/2,5	IEC 61754-2
Optical fibres - part 2-50: class B single-mode fibres	IEC 60793-2-50

Application range

Office, Data centers, Industry

Note

Photographs are not true to scale and do not represent detailed images of the respective products.