DATA SHEET

valid from: 28.09.2021 **H05Z1-K(X05Z1-K)**



Application

4724050

H05Z1-K(X05Z1-K) is a halogen-free, low smoke cable with cross-linked insulation and low emission of corrosive gases. For wiring of lamps, machine tools and splitter and especially for applications where low smoke density and low emission of corrosive gases are required in case of fire.

Application range:

Suitability for the laying inside of conduits installed on or under plaster in case of signal and control current circuits only.

Design

Flammability

Design acc. to EN 50525-3-31

 Certification
 The cable is marked with the ⊲HAR⊳ HAR-sign or HAR-identification thread.

 Conductor
 fine-wire copper conductor acc. to IEC 60228 resp. EN 60228, class 5

 Insulation
 halogen-free, cross-linked compound TI 7 acc. to EN 50363-7

Core identification code different colours

Electrical properties at 20 °C

Nominal voltage U_0/U : 300/500 V Test voltage 2000 V AC

Mechanical and thermal properties

Minimum bending radius at intended use:

AD ≤ 8 mm: 4 x outer diameter

8 mm < AD ≤ 12 mm: 5 x outer diameter

12 mm < AD: 6 x outer diameter

at cautious bending:

AD ≤ 8 mm: 2 x outer diameter

8 mm < AD \leq 12 mm: 3 x outer diameter 12 mm < AD: 4 x outer diameter

Temperature range Fixed installation: -40°C to +70°C During installation: +5 °C to +70 °C

acc. to IEC 60332-1-2 resp. EN 60332-1-2 acc. to EN 50525-1, appendix B; EN 60754-1

Halogen free acc. to EN 50525-1, appendix B; EN 60754
Corrosivity of gases acc. to IEC EN 60754-2 resp. EN 60754-2

Smoke density acc. to EN 61034-2

Tests acc. to IEC 60811 resp. EN 60811, EN 50395 and EN 50396

General requirements These cables are conform to the EU Directive 2014/35/EU (Low Voltage Directive)

Environmental information These cables meet the substance-specific requirements of the EU Directive 2011/65/EU (RoHS).

Note Trade product, no Lapp product