


10540000	<b>DATA SHEET</b>	
Valid from: 18.09.2020	<b>EPIC® H-A32 SS / H-A32 BS DR</b>	

## Description

- H-A inserts with screw termination up to 2.5 mm<sup>2</sup> wire cross section.
- Slim connector insert for standard application.
- Easy to service screw connection.
- Universal for current and voltage transmission.



## General Characteristics

Series	H-A 32
Version	Male/Female (Article 10541000)
Wire Protection	Yes
Number of Contacts	32 + 2 PE
Termination Methods	Screw termination: 0.5 - 2.5 mm <sup>2</sup> (2.5 mm <sup>2</sup> with conductor end sleeves depending on the crimping profile)
Temperature Range	-40°C to +100°C, short-term up to +125°C

## Mechanical Characteristics

Cycle of mechanical operation	100
-------------------------------	-----

## Electrical Characteristics

Rated Voltage, IEC	400V
Rated Voltage, UL	600 V
Rated Voltage, CSA	600 V
Rated Impulse Voltage	4 kV
Rated Current, IEC	16 A
Rated Current, UL	14 A
Rated Current, CSA	16 A
Contact Resistance	1,5 - 4 mOhm
Degree of Soiling	3

## Materials and Surfaces

Contacts	Copper alloy, hard silver-plated
Insulating Body	PC
Flammability Class according to UL 94	V0

## Approvals



UL-Approval, E-File-Number	E75770
----------------------------	--------


## Standard

Safety Standard	IEC 61984, UL 1977, CSA-C22.2 182.3
-----------------	-------------------------------------

Creator: JOKR1/PDP Released: IVSE1/PDP	Document: DB10540000EN Version: 03	Page 1 of 3
---	---------------------------------------	-------------

**Technical Drawings**



10540000	<b>DATA SHEET</b>	
Valid from: 18.09.2020	EPIC <sup>®</sup> H-A32 SS / H-A32 BS DR	



Industrial machinery and plant engineering



Assembly time



Space requirement

**Info**

Slim standard insert, easy to connect by screw  
 Universal for current and voltage transmission

**Application range**

Machine and equipment manufacturings

Control engineering

Use for railway applications - Fire protection in rail vehicles: test in accordance with EN 45545-2. Requirement set R22 u. R23. Danger level HL 1, HI2 u. HL3

**Remark**

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: JOKR1/PDP Released: IVSE1/PDP	Document: DB10540000EN Version: 03	Page 3 of 3
---	---------------------------------------	-------------