19083000	DATA SHEET	Ø I ADD
Valid from: 17.09.2018	EPIC [®] H-B 16 TSB	WLAPP

Description

- The housing standard.
- Wide choice for all applications.



General Characteristics

H-B 16 Series Version Hood M 25 Locking Double lever

Gland body Yes Cable entry Side

Protection (DIN EN 60529) IP 65 (latched) Protection (NEMA 250, UL50E) 4, 12 (latched)

-40°C to +100°C, short term up to +125°C Temperature Range

Materials and Surfaces

Housing Aluminium alloy, powder-coated, grey Bolt Heat-treatable steel, zinc-plated

Lever Steel, zinc-plated Gland body Brass, nickel plated

Approvals

VDE-Approval, VDE-REG.-Nr. B437

Standard

Safety Standard IEC 61984


DATA SHEET 19083000 EPIC® H-B 16 TSB Valid from:




Technical Drawings

17.09.2018











Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Universal, robust metal housings size H-B 16

Application range

Plant engineering Light & sound technology Plastics industry

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB19083000EN	Page 2 of 2
Released: IVSE1/PDP	Version: 01	