


7038880	DATA SHEET	
valid from: 01.01.2019	UNITRONIC® SENSOR Li9Y11Y 3x0,75 + 4x0,34	

Application

UNITRONIC® SENSOR Li9Y11Y 3x0,75 + 4x0,34 is a cable for high flexible applications in power chains. It is intended for combined usage for power supply and sensor/actuator signal transmission. The PP-insulation and the PUR sheath are halogen free.

Design

Design	based on UL AWM Style 10493 (Insulation) and 21198 (Jacket), UL 758, CSA C22.2 No. 210 (80°C, 300 V)
Certification	UL AWM Style 21198 (File No. E63634), UL 758 cRUus AWM I/II A/B (File No. E63634)
Conductor	data core 0.34 mm ² : bare copper, fine-wire stranded, Ø ca. 0.75 mm
Insulation	power supply core 0.75 mm ² : bare copper, fine-wire stranded, ca. 1.1 mm Ø
	data core 0.34 mm ² : polypropylene, wall thickness ca. 0.25 mm, core Ø ca. 1.25 mm
Core identification code	Energieversorgungsader 0.75 mm ² : polypropylene, wall thickness ca. 0.3 mm, core Ø ca. 1.7 mm
	data cores 0.34 mm ² : white, green, yellow, grey
Stranding	Energieversorgungsadern 0.75 mm ² : brown, blue, green/yellow
	3 cores for power supply and 4 data cores stranded around central PP-filler stranding Ø: ca. 4.8 mm wrapping: 1 layer non-woven tape
Outer sheath	PUR, black (similar to RAL 9005), wall thickness: ca. 0.8 mm outer Ø: ca. 6.6 mm

Electrical properties at 20°C

Conductor resistance	0.34 mm ² : max. 54.1 Ω/km 0.75 mm ² : max. 26.0 Ω/km
Peak operating voltage	UL: 300 V
Test voltage	C/C: 2000 V

Mechanical and thermal properties

Minimum bending radius	moved: 10 x cable Ø fixed installation: 5 x cable Ø
Temperature range	Moved: - 5 °C up to +80 °C Fixed installation: - 40 °C up to +80 °C
Flammability	flame retardant acc. to UL 1581 FT-2
Halogen free	according to VDE 0472-815
General requirements	This cable is conform to the EU-Directive 2011/65/EU (RoHS, Restriction of the use of certain hazardous substances).

Creator: PESA / PDC	Document: DB7038880EN	Page 1 of 1
Released: ALTE / PDC	Version: 03	