Valid from: 25.03.2021



Description

- Innovative metal housing
- For safe connections in the smallest possible space
- EMC protection
- Crorrosion-resistant

General characteristics

Series	ULTRA H-A 3
Version	Hood
Locking mechanism	Bolts for single lever
Cable gland	Integrated
Clamping range	5 – 9 mm
Protection rating (DIN EN 60529)	IP 66 (latched) IP 68 - 1 meter / 10 hours (latched)
Protection rating (NEMA 250, UL50E)	4, 4X, 12 (latched)
Temperature range	-40 °C to +100 °C, short-term up to +125 °C
Holding screws for inserts included	yes

Materials and surfaces

Zinc die-casting
Nickel-plated
Brass, nickel-plated
Polyamide
CR
Stainless steel

Standard

Safety Standard

IEC 61984

Approvals

cURus and VDE in preparation.

Creator: TODV1/PDP Released: VACH1/PDP	Document: DB10423650EN Version: 00	Page 1 of 2	
We reserve all rights according to DIN ISO 16016.			
PD 0019/05_04.18EN			






Valid from: 25.03.2021


EPIC[®] ULTRA H-A 3 TSV

Technical Drawings





Robust



Info

EMC protection, Corrosion-resistant, Compact, robust metal housings size H-A 3

Application range

In EMC-sensitive environments, For fixed and flexible applications (e.g. machinery building, wind turbines), Construction machinery, Electric motor manufacturing

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: TODV1/PDP	Document: DB10423650EN	
Released: VACH1/PDP	Version: 00	Page 2 of 2
We reserve all rights according to DIN ISO 16016		