Valid from: 17.09.2018

EPIC[®] SIGNAL M23 SEM/BEM 12P



Description

- Inserts for M23 circular connectors
- Inserts with solder pins at the connection side for soldering in PCB boards.
- Ideal in combination with M23 housings of type B1/B2 for rear wall-mounting.



General characteristics

Series	SIGNAL M23
Version	E-part = rotation to the right (clockwise) /
	P-part = rotation to the left (anticlockwise)
Number of contacts	12
	Solder termination; solder pins with Ø 1.0 mm for
Termination method	PCB soldering.
	Pin length from rear edge of housing B1/B2: 4 mm
Temperature range	-25 to +125 °C
Contacts included	ја

Product variations

Article no.	Version	Contacts
44420107	P-Part	male contacts, PCB solder
44420108	P-Part	female contacts, PCB solder
44420066	E-Part	male contacts, PCB solder
44420106	E-Part	female contacts, PCB solder

Mechanical characteristics

100			
Electrical characteristics			
100 V			
1,5 kV			
7 A			
< 4 mOhm			
3			
Materials and surfaces			
РА			
brass			
Au			
IEC61984			

Creator: MANA2/PDP	Document: DB44420107EN	Desc 1 of 2
Released: IVSE1/PDP	Version: 02	Page 1 of 3
We reserve all rights according to DIN ISO 16016		

DATA SHEET

Valid from: 17.09.2018


EPIC[®] SIGNAL M23 SEM/BEM 12P




Drawings











Creator: MANA2/PDP	Document: DB44420107EN	
Released: IVSE1/PDP	Version: 02	Page 2 of 3
We are a more all eighter an englished to DIN 100 10010		

DATA SHEET

Valid from: 17.09.2018

EPIC[®] SIGNAL M23 SEM/BEM 12P





Good chemical resistance



Industrial machinery and plant engineering



Mechanical resistance



Assembly time



Robust

企

Wind Energy



Variety of approval certifications

Info

With solder pins for PCB boards Only for housing type A1, B1, B2

Application range

Plant engineering Measurement and control technology Apparatus construction

Remark

The inserts are suitable for both male and female contacts. For a complete connection, you will need one P-component and one E-component. P-component = left turning (anticlockwise), E-component = right turning (clockwise) Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB44420107EN	Daga 2 af 2
Released: IVSE1/PDP	Version: 02	Page 3 of 3
We recerve all rights according to DIN ISO 16016		