Valid from: 17.09.2018

EPIC[®] MHB 20 CM



Description

- Double module 20-pin for control signals
- Crimp connection for permanent vibration-proof contact
- EPIC[®] MH system is mateable with the market standard
- The mix of different functions is one plug guarantees high flexibility



General characteristics

Contact type	socket	
Number of contacts	20	
Mating cycles	500	
Material	Polyamide, glass fibre-reinforced	
Inflammability class acc. with UL 94	V0	
Pollution degree	3	
Temperatue range	-40° C to +125° C	
Termination methods	crimp termination: 0.14 – 4.00 mm ²	
Suitable frame	EPIC [®] MH 6 multi-frame EPIC [®] MH 10 multi-frame EPIC [®] MH 16 multi-frame EPIC [®] MH 24 multi-frame	
Suitable contacts	$\operatorname{EPIC}^{^{(\!\!R\!)}}$ H-BE 2.5 machined contacts	

Electrical characteristics

Rated voltage	500 V
Contact resistance	< 5 mΩ
Rated impuls voltage	6 kV
Rated current	16 A

Standards/Approvals


Fire protection on railway vehicles	according EN 45545-2
	requirement sets R22 and R23
	hazard level HL1, HL2 and HL3


Creator: JOKR1/PDP	Document: DB44423227EN	Dess 1 of 2	
Released: IVSE1/PDP	Version: 02	Page 1 of 2	
We recerve all rights according to DIN ISO 16016			



Valid from: 17.09.2018

Drawings





Note

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: JOKR1/PDP	Document: DB44423227EN	Page 2 of 2		
Released: IVSE1/PDP	Version: 02	Page 2 of 2		
We recerve all rights according to DIN ISO 16016				