


19578000	DATA SHEET	
Valid from: 29.08.2022	EPIC® H-A 32 TSB	

Description

- The large, robust housing for two inserts of size 16.



General Characteristics

Series	H-A 32
Version	Hood
Locking	Double lever
Cable entry	1x lateral, see table
Gland body	See table
Protection (DIN EN 60529)	IP 65 (latched)
Temperature Range	-40°C to +100°C, short term up to +125°C

Materials / Surfaces

Housing	Aluminium alloy, powder-coated, grey
Locking	Steel, zinc-plated
Gland body	Brass, nickel-plated


Standard

Safety Standard	IEC 61984
-----------------	-----------


Versions

Article number	Article description	Cable entry	Gland body
10578000	EPIC® H-A 32 TSB 21 ZW	Pg 21	Yes
10579000	EPIC® H-A 32 TSB 29 ZW	Pg 29	Yes
19578000	EPIC® H-A 32 TSB M25	M25	No
19579000	EPIC® H-A 32 TSB M32	M32	No

Creator: BEGE1/PDP Released: IVSE1/PDP	Document: DB19578000EN Version: 00	Page 1 of 2
---	---------------------------------------	-------------

19578000	DATA SHEET	
Valid from: 29.08.2022	EPIC® H-A 32 TSB	

Technical Drawings



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Application range

Machine and equipment manufacturing, Control engineering

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: BEGE1/PDP Released: IVSE1/PDP	Document: DB19578000EN Version: 00	Page 2 of 2
---	---------------------------------------	-------------