Valid from: 14.01.2019



Description

- H-A inserts, easy to service, with screw termination up to 2.5 mm² wire cross section
- The small H-A is used whenever there is minimal space
- Easy cable connection with strait cable entry in the contacts.
- Optimally matched components
- Reduced ordering effort
- No wrong orders

Components of the combination

n

75009620

H-A 3 MAgs (10423500)

H-A 4 BS (10432000)

Article number of the combination Housing Insert

General characteristics

Series Version Connection type Pin-arrangement Contact diameter Termination cross section

Degree of protection (DIN EN 60529) Degree of protection (NEMA 250/UL 50E) Cycles of mechanical operation Temperature range

Materials and surfaces

HousingZinc die-castingsurface HousingPowder-coating, greyInsertPAContact, base materialCopper alloyContact, surfaceHard-silver

Electrical characteristics

Rated Voltage, IEC	400 V
Rated Voltage, UL	600 V
Rated Voltage, CSA	600 V
Rated Impulse Voltage	4 kV
Rated Current, IEC	23 A
Rated Current, UL	10 A
Rated Current, CSA	10 A
Contact Resistance	1,5 - 4 mOhm
Degree of Soiling	3

 Creator: JOKR1/PDP
 Document: DB75009620EN
 Page 1 of 3

 Released: IVSE1/PDP
 Version: 01
 Page 1 of 3



H-A 4 Female Screw termination 4 + PE 1 mm Screw termination: 0,5 - 2,5 mm² (2,5 mm² with wire end sleeve, depending on crimp profile) IP 65 (latched) 12, 4 (latched) 100 -40°C to +125°C, short term up to +125 **DATA SHEET**

Valid from: 14.01.2019



Approvals

VDE-Approval, VDE-REG.-Nr. UL File Number CSA File Number



B437 E75770 053004


Standards

Safety Standard


IEC 61984; UL 1977; CSA-C22.02


Technical Drawings

Housing



Insert







Industrial machinery and plant engineering

Creator: JOKR1/PDP	Document: DB75009620EN	Page 2 of 3		
Released: IVSE1/PDP	Version: 01			
We reserve all rights according to DIN ISO 16016				

DATA SHEET

Valid from: 14.01.2019





Mechanical resistance





Robust



Waterproof



Assembly time



Space requirement

Info

Compact, robust metal housings size H-A 3 Robust power supply connector Straight cable entry into the contacts

Application range

Machine and equipment manufacturing Control engineering Electronic laboratory

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

	Creator: JOKR1/PDP	Document: DB75009620EN	Page 3 of 3
	Released: IVSE1/PDP	Version: 01	
We reserve all rights according to DIN ISO 16016			