75009628

DATA SHEET

Valid from: 24.04.2019

EPIC® KIT H-A 10 BS SGR M20



Description

- H-A inserts, easy to service, with screw termination up to 2.5 mm² wire cross section
- The small H-A is used whenever there is minimal space
- Easy cable connection with strait cable entry in the contacts.
- Optimally matched components
- Reduced ordering effort
- No wrong orders





Components of the combination

Article number of the combination 75009628

Housing H-A 10 SGR M20 (19448100) Insert H-A 10 BS (10441100)

General characteristics

Series H-A 10 Version Female

Connection type Screw termination

Pin-arrangement 10 + PE Contact diameter 2,5 mm

Termination cross section Screw termination: 0,5 – 2,5 mm²

Degree of protection (DIN EN 60529) IP 65 (latched)
Degree of protection (NEMA 250/UL 50E) 12, 4 (latched)

Cycles of mechanical operation 100

Temperature range -40°C to +125°C, short term up to +125

Materials and surfaces

Housing Zinc die-casting
Housing, surface Powder-coating, grey

Insert PBT

Contact, base material Copper alloy Contact, surface Hard-silver

Electrical characteristics

Rated Voltage, IEC 400 V
Rated Voltage, UL 600 V
Rated Voltage, CSA 600 V
Rated Impulse Voltage 4 kV
Rated Current, IEC 16 A
Rated Current, UL 16 A
Rated Current, CSA 16 A

Contact Resistance 1,5 - 4 mOhm

Degree of Soiling

Creator: JOKR1/PDP	Document: DB75009628EN	Page 1 of 3
Released: IVSE1/PDP	Version: 02	

75009628

Valid from: 24.04.2019

EPIC® KIT H-A 10 BS SGR M20

DATA SHEET



Approvals

VDE-Approval, VDE-REG.-Nr. UL File Number

B437 E75770






Standards

Safety Standard

IEC 61984; UL 1977; CSA-C22.2 182.3


Technical Drawings:

Housing




Insert

Pin assignment:



Dimensions:



Creator: JOKR1/PDP Document: DB75009628EN Page 2 of 3 Released: IVSE1/PDP Version: 02

75009628

EPIC[®] KIT H-A 10 BS SGR M20

DATA SHEET



Valid from: 24.04.2019



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof



Assembly time



Space requirement

Info

Compact, robust metal housings size H-A 10 Robust power supply connector Straight cable entry into the contacts

Application range

Machine and equipment manufacturing Control engineering Electronic laboratory

Remark

Photographs are not to scale and do not represent detailed images of the respective products.