75009690

DATA SHEET

Valid from: 18.09.2020

EPIC® POWER LS 1 KIT D6 6 PINS FEMALE



Description

- Circular connector for servomotors and power supply
- High power at smallest installation space
- · Optimal solution for electric motors
- EMC-optimised design
- Safety use in field environment by high protection class
- Complete connector with housing and insulation body, equipped with suitable crimp contacts



General Characteristics

Series POWER LS 1

Version Cable connector for female contacts

Pin configuration 5+PE
Rated voltage (V) 630 V
Rated impulse voltage 6 kV
Rated current (A) 25 A
Contact resistance <4 mOhm

Contacts Gold plated brass

Number of contacts 5+PE

Termination methods Crimp termination: 0.5 – 2,5 mm²

Protection IP 68 (latched)

Cycle of mechanical operation 500

Temperature range -25°C to +125°C

Degree of soiling 3

Materials and Surfaces

Housing Nickel-plated zinc die-casting, nickel-plated brass

Insert PA

Seal FPM/FKM
Contacts Brass
Contact surface Au

Approvals

VDE-Approval, VDE-REG.-Nr. B025 UL-File-Number E249137

Standard

Safety Standard IEC 61984, UL 2238, CSA C22.2 182.3



Creator: STKU3/PDP Document: DB75009690EN
Released: IVSE1/PDP Version: 02
Page 1 of 3


75009690

DATA SHEET

Valid from: 18.09.2020

EPIC® POWER LS1 KIT D6 6 PINS FEMALE







Good chemical resistance



Corrosion-resistant



Industrial machinery and plant engineering



Maximum vibration protection



Mechanical resistance



Assembly time



Optimum strain relief



Space requirement



Robust

Creator: STKU3/PDP	Document: DB75009690EN	Page 2 of 3
Released: IVSE1/PDP	Version: 02	

75009690 DATA SHEET

Valid from: 18.09.2020

EPIC[®] POWER LS 1 KIT D6 6 PINS FEMALE





Integrated SKINTOP® cable gland



Waterproof



Wind Energy



Variety of approval certifications

Application range

Plant engineering Servo drives and servo assemblies

Remark

Photographs are not to scale and do not represent detailed images of the respective products.