DATA SHEET

Gültig ab: 03.11.2020



Description

- Inserts of the EPIC[®] H-BE series are regarded as classics in the industry and are ideal for use at higher voltages and currents.
- Crimp termination creates a vibration-proof connection, ensures maximum contact reliability between contact and wire and is suitable for automated assembly.
- Can be used in rail vehicles in conformity with standards (test of fire behavior according to DIN EN 45545-2:2016-02, requirement set R22 and R23, hazard levels HL1, HL2 and HL3).
- In the EPIC[®] H-BE series, inserts of different connection types within the same size can be combined as desired (screw, crimp, cage clamp or push-in).



General Characteristics

Series	H-BE 48 for machined crimp contacts	
Version	Male (Article No. 10187002)	
	Female (Article No. 10187002)	
Number of Contacts	48 + 2 PE	
Termination Methods	Crimp termination: 0.14 – 4.0 mm ² (AWG 26–AWG 12)	
Temperature Range	-40° to +125°C	

Mechanical Characteristics

Cycle of mechanical	operation	≥ 500
Cycle of mechanical	operation	≥ 500

Electrical Characteristics

Rated Voltage, IEC	500 V
Rated Voltage, UL	600 V
Rated Voltage, CSA	600 V
Rated Impulse Voltage	6 kV
Rated Current, IEC	16 A
Rated Current, UL	16 A
Rated Current, CSA	16 A
Contact Resistance	≤ 5 mOhm
Degree of Soiling	3

Materials and Surfaces

Contacts	Copper alloy, hard silver-plated / hard gold-plated
Insulating Body	PC
Flammability Class according to UL 94	V0

Approvals

UL-Approval, E-File-Number

E75770



	Creator: STKU3/PDP	Document: DB10186202EN	Daga 1 of 2
	Released: IVSE1/PDP	Version: 01	Page 1 of 3
We reserve all rights apporting to DIN ISO 16016			

DATA SHEET

Gültig ab: 03.11.2020



Standard

Safety Standards


Railway applications Fire protection on railway vehicles


Railway applications Rolling stock equipment Shock and vibration tests IEC 61984, UL 1977, CSA-C22.2 No. 182.3


DIN EN 45545-2:2016-02 Requirement sets R22 and R23, Hazard level HL1, HL2 and HL3)


DIN EN 61373 Category 2

Technical Drawings











Maschinen- und Anlagenbau



 Creator: STKU3/PDP
 Document: DB10186202EN
 Page 2 of 3

 Released: IVSE1/PDP
 Version: 01
 Page 2 of 3

Gültig ab: 03.11.2020









Temperature-resistant

Info

Multifunctional insert for versatile appliactions Screw, crimp, cage clamp and Push-In version - freely combinable The default PE-position is next to pin 1. PE-postition can bechanged to the other end of the connector if the changeis made on <u>both</u> connectors (male and female)

Application range

Mechanical engineering; Light & sound technology; Plastics industry, Railway applications / vehicle construction

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Released: IVSE1/PDP	Version: 01	Page 3 of 3
Creator: STKU3/PDP	Document: DB10186202EN	Page 3 of 3