Valid from: 17.09.2018

EPIC<sup>®</sup> H-B 6 TBFH-LB



### Description

- The smallest housing out of the H-B series.
- For inserts with high properties.



#### **General Characteristics**

Series	Н-В 6
Version	Coupler hood M25
Locking	Single lever
Gland body	No
Cable entry	Straight
Protection (DIN EN 60529)	IP 65 (latched)
Protection (NEMA 250, UL50E)	4, 12 (latched)
Temperature Range	-40°C to +100°C, short term up to +125°C

#### **Materials and Surfaces**

Housing	Aluminium alloy, powder-coated, grey	
Bolt	Heat-treatable steel, zinc-plated	
Lever	Steel, zinc-plated	
Profile Seal	NBR	

## Approvals

VDE-Approval, VDE-REG.-Nr.

#### Standard

Safety Standard

B437

IEC 61984

	Creator: MANA2/PDP	Document: DB79010200EN	Daga 1 of 2	
	Released: IVSE1/PDP	Version: 01	Page 1 of 2	
We reserve all rights according to DIN ISO 16016				

Valid from:


EPIC<sup>®</sup> H-B 6 TBFH-LB

**S LAPP** 

# 17.09.2018

## **Technical Drawings**









Automation



Industrial machinery and plant engineering



Mechanical resistance





Robust



Waterproof

Info

Universal, robust metal housings size H-B 6

#### Application range

Plant engineering Control engineering Plastics industry

#### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB79010200EN	Page 2 of 2		
Released: IVSE1/PDP	Version: 01	-		
We reserve all rights according to DIN ISO 16016.				