Valid from: 17.09.2018



### Description

Ideal for many applications due to a wide range of housings and inserts



### **General Characteristics**

Series	H-B 24
Version	Surface mount base M32
Protection cover	Yes
Locking	Bolts for double lever
Cable entry	1
Protection (DIN EN 60529)	IP 65 (latched) IP 40 (cover closed)
Protection (NEMA 250, UL50E)	4, 12 (latched)
Temperature Range	-40°C to +100°C, short term up to +125°C
Materials and Surfaces	

Housing	Aluminium alloy, powder-coated, grey
Cover	Zinc alloy, powder-coated, grey
Bolt	Zinc-plated steel
Sealing	NBR

# Approvals

VDE-Approval, VDE-REG.-Nr.

### Standard

Safety Standard

B437

IEC 61984

Creator: MANA2/PDP	Document: DB79145400EN	Page 1 of 2		
Released: IVSE1/PDP	Version: 02			
We reserve all rights according to DIN ISO 16016				




Valid from: 17.09.2018

EPIC<sup>®</sup> H-B 24 SDRH-BO

# **Technical Drawings**









Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info Universal, robust metal housings size H-B 24

### Application range

Plant engineering Light & sound technology Plastics industry

#### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

	Creator: MANA2/PDP Released: IVSE1/PDP	Document: DB79145400EN Version: 02	Page 2 of 2	
We reserve all rights according to DIN ISO 16016.				