# 10542100 DATA SHEET

EPIC® H-A 48 SS / H-A 48 BS



### Description

Valid from:

18.09.2020

- H-A inserts with screw termination up to 2.5 mm<sup>2</sup> wire cross section.
- Slim connector insert for standard application.
- Easy to service screw connection.
- Universal for current and voltage transmission.



### **General Characteristics**

Series H-A 48

Version Male/Female(Article 10543100)

Wire Protection No

Number of Contacts 48 + 3 PE

Screw termination: 0.5 - 2.5 mm<sup>2</sup> (2.5 mm<sup>2</sup> with

Termination Methods conductor end sleeves depending on the crimping

profile)

Protection (DIN EN 60529) IP 65, latched to the housing Protection (NEMA 250, UL50E) 4, 12, latched to the housing

Temperature Range -40°C to +100°C, short-term up to +125°C

**Mechanical Characteristics** 

Cycle of mechanical operation 100

**Electrical Characteristics** 

Rated Voltage, IEC 400 V
Rated Voltage, UL 600 V
Rated Voltage, CSA 600 V
Rated Impulse Voltage 4 kV
Rated Current, IEC 16 A
Rated Current, UL 14 A
Rated Current, CSA 16 A

Contact Resistance 1,5 - 4 mOhm

Degree of Soiling 3

**Materials and Surfaces** 

Contacts Copper alloy, hard silver-plated

Insulating Body PBT Flammability Class according to UL 94 V0

Standard

Safety Standard IEC 61984, UL 1977, CSA-C22.2 182.3

Creator: STKU3/PDP	Document: DB10542100EN	Page 1 of 3
Released: IVSE1/PDP	Version: 02	

### 10542100

## DATA SHEET


Valid from: 18.09.2020


 $\mathsf{EPIC}^{\scriptscriptstyle{(\! R)}}\,\mathsf{H-A}\;\mathsf{48}\;\mathsf{SS}\;/\;\mathsf{H-A}\;\mathsf{48}\;\mathsf{BS}$ 




### **Technical Drawings**









Creator: STKU3/PDP	Document: DB10542100EN	Page 2 of 3
Released: IVSE1/PDP	Version: 02	

# 10542100 DATA SHEET

Valid from: 18.09.2020

### EPIC® H-A 48 SS / H-A 48 BS







Industrial machinery and plant engineering



Assembly time



Space requirement

### Info

Slim standard insert, easy to connect by screw Universal for current and voltage transmission

### **Application range**

Machine and equipment manufacturings Control engineering

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.