75009614

DATA SHEET

Valid from: 14.01.2019

EPIC® KIT H-A 4 SS MTGV M20



Description

- H-A inserts, easy to service, with screw termination up to 2.5 mm² wire cross section
- The small H-A is used whenever there is minimal space
- Easy cable connection with strait cable entry in the contacts.
- Optimally matched components
- · Reduced ordering effort
- No wrong orders



Components of the combination

Article number of the combination 75009614

Housing H-A 3 MTgv M20 (19512100) Insert H-A 4 SS (10431000)

General characteristics

Series H-A 4 Version Male

Connection type Screw termination

Pin-arrangement 4 + PE Contact diameter 1 mm

Termination cross section Screw termination: 0,5 – 2,5 mm² (2,5 mm² with wire end sleeve,

depending on crimp profile)

Degree of protection (DIN EN 60529) IP 65 (latched)
Degree of protection (NEMA 250/UL 50E) 12, 4 (latched)

Cycles of mechanical operation 100

Temperature range -40°C to +125°C, short term up to +125

Materials and surfaces

Housing, base material Zinc die-casting surface Housing Powder-coating, grey

Insert PA

Contact, base material Copper alloy Contact, surface Hard-silver

Electrical characteristics

Rated Voltage, IEC 400 V
Rated Voltage, UL 600 V
Rated Voltage, CSA 600 V
Rated Impulse Voltage 4 kV
Rated Current, IEC 23 A
Rated Current, UL 10 A
Rated Current, CSA 10 A

Contact Resistance 1,5 - 4 mOhm

Creator: JOKR1/PDP	Document: DB75009614EN	Page 1 of 3
Released: IVSE1/PDP	Version: 01	

DATA SHEET

Valid from: 14.01.2019

75009614

EPIC® KIT H-A 4 SS MTGV M20



Degree of Soiling

3

Approvals

VDE-Approval, VDE-REG.-Nr. B437
UL File Number E75770
CSA File Number 053004








Standards

Safety Standard


IEC 61984; UL 1977; CSA-C22.02


Technical Drawings

Housing



Insert





Creator: JOKR1/PDP Document: DB75009614EN
Released: IVSE1/PDP Version: 01

Page 2 of 3

75009614

DATA SHEET

Valid from: 14.01.2019

EPIC® KIT H-A 4 SS MTGV M20





Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof



Assembly time



Space requirement

Info

Compact, robust metal housings size H-A 3 Robust power supply connector Straight cable entry into the contacts

Application range

Machine and equipment manufacturing Control engineering Electronic laboratory

Remark

Photographs are not to scale and do not represent detailed images of the respective products.