0156001 DATA SHEET

Valid from: 01.04.2019

DIN compensating cable KNL Y XX x 1,5



Application

The compensating cables KNL Version Y $XX \times 1,5$ mm² are multi-cored PVC insulated cables which transmit the thermoelectric voltage of NiCr/Ni thermocouples. They are for flexible use and fixed installation in dry and damp rooms with medium mechanical load. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range.

Design

Conductor 1.5 mm² (48 x 0.20 mm)

Conductor material KCA alloying, accuracy class 2 according DIN 43722

Positive conductor: Fe (iron)

Negative conductor: CuNi (cupronickel)

Core insulation PVC compound

Core identification Positive conductor: red

Negative conductor: green

Core layering Cores twisted together

Outer sheath PVC compound, colour: green

Electrical properties

Limiting deviation class 2 ±100 µV (±2.5 °C) / measuring point temperature +900 °C

Mechanical and thermal properties

Temperature range fixed installed: -40 °C up to +80 °C

occasional flexing: -5 °C up to +70 °C

Minimum bending radius occasional flexing: 12 x cable diameter

Flammability flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2