## 75009645

# **DATA SHEET**

Valid from: 25.02.2019

EPIC® Kit H-BE 16 SS TG M25



## Description

- Optimally matched components.
- H-BE inserts with screw termination up to 2.5 mm<sup>2</sup> connection cross-section.
- The possibility of using higher voltages and currents as well as high reliability characterizes the EPIC® H-BE series.
- Reduced order costs. No wrong orders.





## Components

Item number of the combination 75009645

Housing EPIC® H-B 16 TG M25 (19080000)
Insert EPIC® H-BE 16 SS DR (10194000)

### **General characteristics**

Insert H-BE 16
Gender Male

Connection type Screw termination
Connection cross-section 0.5 – 2.5 mm<sup>2</sup>

Wire protection Yes
Number of contacts 16 + PE
Contact diameter 2,5 mm
Mating cycles 500

Temperature range -40°C to +100°C, short-term up to +125 °C

Housing Hood Gland body No

Cable entry 1x straight

Locking Bolt for double lever
Protection (DIN EN 60529) IP 65 (mated and latched)
Protection (NEMA 250/UL50E) 4 and 12 (mated and latched)

#### **Electrical characteristics**

500 V Rated voltage, IEC Rated voltage, UL 600 V Rated voltage, CSA 600 V Rated impulse voltage 6 kV Rated current, IEC 16 A Rated current, UL 16 A Rated current, CSA 16 A < 2 mOhm Contact resistance

Creator: BEGE1/PDP	Dokument: DB75009645EN	Page 1 of 3
Released: IVSE1/PDP	Version: 02	

Degree of soiling

## 75009645

# **DATA SHEET**

#### Valid from: 25.02.2019

EPIC® Kit H-BE 16 SS TG M25



## Materials/Surfaces

Contacts Copper alloy, hard silver plated

PC Insulating body Flammability class according to UL94 V0

Housing Aluminium alloy, powder-coated (grey)

Locking Steel, zinc-plated

Housing seal Gland body

## **Approvals**

VDE-Approval, VDE-REG.-Nr. B437 UL File Nummer E75770 **CSA File Nummer** 053004









### **Standards**

Safety standards IEC 61984; UL 1977; CSA-C22.2

### **Technical drawings**

Housing dimensions





# 75009645 DATA SHEET

Valid from: 25.02.2019

# EPIC® Kit H-BE 16 SS TG M25





Insert

Pin assignment

**Dimensions** 









Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof



Temperature-resistant

#### Info

Universal, robust metal housings Multifunctional insert for versatile appliactions

# **Application range**

Plant engineering, control engineering, plastics industry, light & sound technology

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: BEGE1/PDP	Dokument: DB75009645EN	Page 3 of 3
Released: IVSE1/PDP	Version: 02	