

DATA SHEET

01570XX

DIN compensating cable KPL Y XX x 1,5

valid from:

01.12.2008

Application

The compensating cables KPL Version Y XX x 1,5 mm² are multi-cored PVC insulated cables which transmit the thermoelectric voltage of PtRh/Pt thermocouples. They are for flexible use and fixed installation in dry and damp rooms with medium mechanical load. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range.

Design

Conductor 1,5 mm² (48 x 0,20 mm)

Conductor material RCB/SCB alloying, accuracy class 2 according DIN 43722

Positive conductor: Cu (copper)

Negative conductor: CuNi (cupronickel)

Core insulation PVC compound

Core identification Positive conductor: red

Negative conductor: white

Core layering Cores twisted together

Outer sheath PVC compound, colour: white

Electrical properties

Limiting deviation class 2 ± 60 µV (± 5,0 ℃) / me asuring point temperature +1000 ℃

Mechanical and thermal properties

Temperature range fixed installed: $-40 \, \text{C}$ upto $+80 \, \text{C}$

occasional flexing: -5 ℃ up to +70 ℃

Minimum bending radius occasional flexing: 12 x cable diameter

Flammability flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2