Valid from: 25.02.2019

EPIC[®] Kit H-BE 16 BS SGR M25



Description

- Optimally matched components.
- H-BE inserts with screw termination up to 2.5 mm² connection cross-section.
- The possibility of using higher voltages and currents as well as high reliability characterizes the EPIC® H-BE series.
- Reduced order costs. No wrong orders.

Components

Item number of the combination Housing Insert 75009648 EPIC® H-B 16 SGR M25 (19074000) EPIC® H-BE 16 BS DR (10195000)

General characteristics

Insert Gender Connection type Connection cross-section Wire protection Number of contacts Contact diameter Mating cycles Temperature range

Housing Gland body Cable entry

Locking

H-BE 16 Female Screw termination 0.5 - 2.5 mm² Yes 16 + PE 2,5 mm 500 -40°C to +100°C, short-term up to +125 °C

Surface mount base

1x lateral Double lever IP 65 (mated and latched) 4 and 12 (mated and latched)

Electrical characteristics

Protection (NEMA 250/UL50E)

Protection (DIN EN 60529)

Rated voltage, IEC	500 V
Rated voltage, UL	600 V
Rated voltage, CSA	600 V
Rated impulse voltage	6 kV
Rated current, IEC	16 A
Rated current, UL	16 A
Rated current, CSA	16 A
Contact resistance	< 2 mOhm
Degree of soiling	3

Creator: BEGE1/PDP	Dokument: DB75009648EN	Daga 1 af 2	
Released: IVSE1/PDP	Version: 02	Page 1 of 3	
We reserve all rights according to DIN ISO 16016			

Valid from: 25.02.2019



Materials/Surfaces

Contacts Insulating body Flammability class according to UL94 Copper alloy, hard silver plated PC V0

Aluminium alloy, powder-coated (grey) Steel, zinc-plated NBR

Approvals

Housing seal

Gland body

Housing

Locking

VDE-Approval, VDE-REGNr.	B437
UL File Nummer	E75770
CSA File Nummer	053004




Standards

Safety standards

IEC 61984; UL 1977; CSA-C22.2

Technical drawings

Housing dimensions



Creator: BEGE1/PDP	Dokument: DB75009648EN	
Released: IVSE1/PDP	Version: 02	Page 2 of 3
We recerve all rights according to DIN ISO 16016		


DATA SHEET




Valid from: 25.02.2019

EPIC[®] Kit H-BE 16 BS SGR M25

Insert Pin assignment



Dimensions



To

Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof



Info Universal, robust metal housings Multifunctional insert for versatile appliactions

Temperature-resistant

Application range

Plant engineering, control engineering, plastics industry, light & sound technology

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: BEGE1/PDP Released: IVSE1/PDP	Dokument: DB75009648EN Version: 02	Page 3 of 3		
We reserve all rights according to DIN ISO 16016.				