Valid from: 01.04.2019

IEC compensating cable KNL Y XX x 1,5



## Application

The compensating cables KNL Version Y XX x 1,5 mm<sup>2</sup> are multi-cored, PVC insulated cables which transmit the thermoelectric voltage of NiCr/Ni thermocouples. They are for flexible use and fixed installation in dry and damp rooms with medium mechanical load. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range.

## Design

Conductor	1.5 mm² (48 x 0.20 mm)	
Conductor material	KCA alloying, accuracy class 2 acc Positive conductor: Negative conductor:	cording IEC 60584 Fe (iron) CuNi (cupronickel)
Core insulation	PVC compound	
Core identification	Positive conductor: Negative conductor:	green white
Core layering	Cores twisted together	
Outer sheath	PVC compound, colour:	green

## **Electrical properties**

Limiting deviation class 2 $\pm 100 \mu$	(±2.5 °C) / measuring point temperature +900 °C
------------------------------------------	-------------------------------------------------

## Mechanical and thermal properties

Temperature range	fixed installed: occasional flexing:	-40 °C up to +80 °C -5 °C up to +70 °C
Minimum bending radius	occasional flexing:	12 x cable diameter
Flammability	flame retardant in acc. to IEC 6033	32-1-2 resp. VDE 0482-332-1-2

Creator: TOME/PCM	Document: DB0166001EN	Page 1 of 1
Released: ALTE/PDC	Version: 04	Page 1 of 1