# 0167501 DATA SHEET

Valid from: 01.04.2019

IEC compensating cable KPL SY XX x 1,5



## **Application**

The compensating cables KPL Version SY XX x 1,5 mm<sup>2</sup> are multi-cored, PVC insulated cables with steel wire armouring which transmit the thermoelectric voltage of PtRh/Pt thermocouples. They are for flexible use and fixed installation in dry and damp rooms with medium mechanical load. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range. The steel wire armouring serves as mechanical protection.

### Design

Conductor 1.5 mm<sup>2</sup> (48 x 0.20 mm)

Conductor material RCB/SCB alloying, accuracy class 2 according IEC 60584

Positive conductor: Cu (copper)

Negative conductor: CuNi (cupronickel)

Core insulation PVC compound

Core identification Positive conductor: orange

Negative conductor: white

Core layering Cores twisted together

Inner sheath PVC compound, colour: orange

Armouring Galvanized steel wire braiding

Outer sheath PVC compound, colour: orange

### **Electrical properties**

Limiting deviation class 2 ±60 µV (±5.0 °C) / measuring point temperature +1000 °C

### Mechanical and thermal properties

Temperature range fixed installed: -40 °C up to +80 °C

occasional flexing: -5 °C up to +70 °C

Minimum bending radius occasional flexing: 15 x cable diameter

Flammability flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2

Creator: TOME/PCM	Document: DB0167501EN	Page 1 of 1
Released: ALTE/PDC	Version: 02	