DATA SHEET 1030600

valid from: 2021-04-22

UNITRONIC® LIYCY (TP) BK



Application

UNITRONIC® LIYCY (TP) BK is a screened, twisted pair data cable for low frequency applications. The cable is designed for fixed installation and for conditional flexible use. It can be used in dry and damp rooms and also outdoors.

The twisted pairs with short lay lengths provides good decoupling of the conductor circuits. The screen provides protection against electromagnetic interferences.

The cable is used for example in computer systems, instrumentation technology, office equipment and balances.

Design

Screen

Outer sheath

Design based on standard VDE 0812 and EN 50288-7

Certification EN 13501-6 and EN 50575 Classification of fire behaviour

(article/dimension range see www.lappkabel.com/cpr)

Conductor fine wire strands of bare copper wires

Insulation special PVC-based compound

Core identification code acc. to DIN 47100

Stranding cores twisted to pairs, pairs are stranded in layers,

> wrapping with foil on the outer layer braiding with tinned copper wires

special PVC-based compound colour: black (similar RAL 9005)

Electrical properties at 20 °C

0.14 mm²: max. 138.0 Ω/km Conductor resistance

> 0.25 mm²: max. 79.0 Ω/km 0.34 mm²: max. 57.0 Ω/km 0.5 mm²: max. 39.0 Ω /km 0.75 mm²: max. 26.0 Ω/km 1 mm²: max. 19.5 Ω /km 1.5 mm²: max. 13.3 Ω /km

Specific volume resistivity > 20 G Ω x cm

C/C: approx. 120 nF/km Mutual capacitance

C/S: approx. 160 nF/km

(at 800 Hz)

Inductance approx. 0.65 mH/km

0.14 mm²: 350 V (not for power applications) Maximum operating voltage

> ≥ 0.25 mm²: 500 V (not for power applications) Must not be connected to the mains supply voltage.

Test voltage 0.14 mm²: 1200 V

≥ 0.25 mm²: 1500 V

Mechanical and thermal properties

Temperature range

Minimum bending radius occasional flexing: 15 x outer diameter

fixed installation: 6 x outer diameter occasional flexing: - 5 °C up to +70 °C fixed installation: - 40 °C up to +80 °C

Flammability flame retardant acc. to IEC 60332-1-2 resp. EN 60332-1-2

Weather and UV resistance acc. to EN 50525-1 cables with black outer sheath are suitable

for permanent outdoor use

General requirements These cables are conform to

EU-Directive 2011/65/EU (RoHS, Restriction of the use of certain hazardous

substances) and EU-Directive 2014/35/EU (Low Voltage Directive). A part of these cables (see www.lappkabel.com/cpr) are classified in accordance with the EU-Regulation no. 305/2011 (CPR).

Environmental information These cables meet the substance-specific requirements of the EU Directive 2011/65/EU (RoHS).

Document: DB1030600EN Creator: PESA / PDC Page 1 of 1 Version: 02 Released: ALTE / PDC