

**Thermocouple cable  
K GL-GL NiCr/Ni 2x0,5 IEC oval****DB1161009**  
valid from: 30.09.2015**Application**

The compensating cable K GL-GL NiCr/Ni 2x0,5 mm<sup>2</sup> is a E-glass wrapped thermocouple cable type K which transmits the thermoelectric voltage of NiCr/Ni thermocouples. It is for flexible use and fixed installation in dry rooms. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range.

**Design**

Conductor	0,5mm (solid)
Conductor material	K alloys, according IEC 60584-1 Positive conductor: NiCr (Nickel chromium) Negative conductor: Ni (Nickel)
Core insulation	E-glass
Core identification	Positive conductor: green Negative conductor: white
Outer braid	E-glass Colour: green

**Electrical properties**

Limiting deviation	± 2,5°C (acc. to IEC 60584-1)
Thermocouple tolerances	- 40°C up to +1200°C (acc. to IEC 60584-3)
Test voltage	500 V

**Mechanical and thermal properties**

Minimum bending radius	occasionally flexing: 12 x cable Ø fixed installation: 6 x cable Ø
Temperature range	occasionally flexing: -90°C up to +350°C fixed installation: -90°C up to +400°C
Application temperature range	Type K: -40°C up to +1200°C (acc. to IEC 60584-1) for item 1161009: -40°C up to +400°C (considering the insulation)
Flame retardant	acc. to IEC 60332-1-2