


0154011	DATA SHEET	
Valid from: 01.04.2019	DIN extension cable KE 20 L 2x1,5	

Application

The extension cable KE 20 L 2 x 1,5 mm² is a PVC insulated cable with aluminium foil screen which transmits the thermoelectric voltage of Fe/CuNi thermocouples. It is for flexible use and fixed installation in dry and damp rooms with medium mechanical load. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range. The overlapping foil wrapping screens the cores against electromagnetic interference.

Design

Conductor	1.5 mm ² (48 x 0.20 mm)	
Conductor material	LX alloying, accuracy class 2 according DIN 43722	
	Positive conductor:	Fe (iron)
	Negative conductor:	CuNi (cupronickel)
Core insulation	PVC compound	
Core identification	Positive conductor:	red
	Negative conductor:	blue
Core layering	Cores twisted together	
Screening	aluminium clad plastic foil with tinned copper drain wire (7x0.30 mm)	
Outer sheath	PVC compound, colour:	blue

Electrical properties

Limiting deviation class 2	±140 µV (±2.5 °C) / measuring point temperature +500 °C
----------------------------	---

Mechanical and thermal properties

Temperature range	occasional flexing:	-5 °C up to +70 °C
Minimum bending radius	occasional flexing:	15 x cable diameter
Flammability	flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2	

Creator: TOME/PCM Released: ALTE/PDC	Document: DB0154011EN Version: 02	Page 1 of 1
---	--------------------------------------	-------------

We reserve all rights according to DIN ISO 16016.

PD 0019/05_04.18EN