


21700602	<b>DATA SHEET</b>	
Valid from: 20.09.2023	<b>ED-IE-AX-M12X-6A-67-FC</b>	

### Product description

- Field mountable Industrial Ethernet Connector, M12 X-coded acc. to IEC 61076-2-109
- Suitable for industrial applications
- Robust and consistent against vibration
- No special tools needed



### General characteristics

Ambient temperature	-40 to +85 °C
Protection degree	IP 67*
Termination type	IDC
Outer diameter, cable	5.0 – 9.7 mm**
Outer diameter, wire	0.85 – 1.6 mm
Termination cross section, stranded, 7 wires	AWG26/7 – AWG22/7
Termination cross section, solid	AWG26/1 – AWG22/1
Pollution degree	2
Overvoltage category	III
Torque, cable screw connection	1.5 Nm

\*following Lapp products with an outer diameter greater than 8.5 mm are recommended to enable the protection degree IP67:

ETHERLINE® Cat.6<sub>A</sub>  
ETHERLINE® PN Cat.6<sub>A</sub> FLEX  
ETHERLINE® FD CAT.6<sub>A</sub>  
ETHERLINE® TORSION Cat.6<sub>A</sub>  
ETHERLINE® Cat.7

\*\*following version is recommended for cable outer diameters less than 6.3 mm: 21700644

### Mechanical properties

Insertion force	≤ 30 N
Mating cycles	≥ 100

### Electrical properties

Rated voltage	60 V DC
Current carrying capacity at 40°C	0,5 A
Insulation resistance	≥ 100 MΩ


### Transmission characteristics

Suitable for 10 Gigabit Ethernet acc. to IEEE 802.3an    yes

### Materials

Connector housing, base material	die-cast zinc
Contacts, surface	Ni + Au
Contac holder and stuffer cap	PA UL94-V0 HL3 R22 according to EN 45545-2

Creator: STKU3/PDP Released: IVSE1/PDP	Document: DB21700602EN Version: 07	Page 1 of 2
---	---------------------------------------	-------------

21700602	<b>DATA SHEET</b>	
Valid from: 20.09.2023	<b>ED-IE-AX-M12X-6A-67-FC</b>	

### Approvals

UL listed, E-File

E353543

### Standards

Product standard

DIN EN 61076-2-109


Vibration and Shock

DIN EN 61373:2011-04 Class 1, Category B

Salt-Spray

DIN EN 60068-2-11 02/48H

### Drawings



### Application range

Automation, industrial machinery and plant engineering

### Note

Photographs are not true to scale and do not represent detailed images of the respective products.

Creator: STKU3/PDP Released: IVSE1/PDP	Document: DB21700602EN Version: 07	Page 2 of 2
---	---------------------------------------	-------------