DATA SHEET

valid from: 09.09.2021

1127400

ÖLFLEX® 127 HSLH



Application

ÖLFLEX® 127 HSLH are halogen free, flame retardant control cables for occasional flexible use and fixed installation for medium mechanical use. They are also suitable for use in dry or damp areas, but not outdoors.

They are suitable for occasional, non-automated movements. The maximum tensile load is 15 N/mm² of conductor cross-section during installation and operation. Compulsory guidance is not permitted.

ÖLFLEX® 127 HSLH cables are particularly used in areas, where human and animal life as well as valuable property are exposed to high risk of fire hazards. In the event of a fire minimal toxic and no corrosive gases occur.

Application range: Public buildings, airports, railway stations, plant engineering and construction, air conditioning systems, stage applications

Design

Design based on EN 50525-3-11 and EN 50525-2-51

Certification VDE certified: Supply cable with improved characteristics in the case of fire

EN 13501-6 and EN 50575 Classification of fire behaviour

(article/dimension range see www.lappkabel.com/cpr)

Conductor fine wire strands of bare copper, acc. to IEC 60228 resp. EN 60228, Class 5

Insulation halogen free compound TI6 acc. to EN 50363-7

Core identification code acc. to VDE 0293-1, with or without GN/YE ground conductor

black cores with white numbers acc. to EN 50334

Stranding cores are stranded in layers

Outer sheath halogen free, flame retardand special compound HM2 acc. to VDE 0250-214

Colour: silver grey, similar RAL 7001

Electrical properties at 20 °C

Nominal voltage U_0/U : 300/500 V Test voltage core /core: 4000 V AC

Mechanical and thermal properties

Minimum bending radius occasional flexing: 15 x outer diameter

fixed installation: 4 x outer diameter

Temperature range occasional flexing: -5°C up to +70°C max. conductor temp.

fixed installation: -40°C up to +80°C max. conductor temp.

Flammability flame retardant acc. to IEC 60332-1-2 resp. EN 60332-1-2

no flame-propagation

acc. to IEC 60332-3-22 resp. EN 60332-3-22

acc. to IEC 60332-3-24 resp. EN 60332-3-24 (Cat. C) or acc. to IEC 60332-3-25 resp. EN 60332-3-25 (Cat. D)

Halogen freeacc. to IEC 60754-1 resp. EN 60754-1Corrosivity of gasesacc. to IEC 60754-2 resp. EN 60754-2Smoke densityacc. to IEC 61034-2 resp. EN 61034-2Toxicityacc. to NES 713-3, EN 50306-1 (≤ 6)

Tests acc. to IEC 60811 resp. EN 60811, EN 50395, EN 50396

General requirementsThese cables are conform to the EU-Directive 2014/35/EU (Low Voltage Directive).

A part of these cables (see www.lappkabel.com/cpr) are classified in accordance with the EU-Regulation no. 305/2011 (CPR).

Environmental information These cables meet the substance-specific requirements of the EU Directive 2011/65/EU (RoHS).

Creator: HESC / PDC Document: DB1127400EN

Released: ALTE / PDC Version: 01

Page 1 of 1