



| | | |
|-----------------------------------|---|---|
| 2170273 | DATA SHEET |  |
| valid from: 01.01.2019 | UNITRONIC® BUS CAN FD P 2x2x0,25 | |

Application

UNITRONIC® BUS CAN FD P is a highly flexible data cable with UL and cUL approval, for CAN (Controller Area Network) fieldbus system according to ISO11898 as well as for high performance data networks with 120 Ohms nominal impedance. The second pair can be used for electrical power supply for the logical bus units. The transmission characteristics of the cable conform to the CAN system and guarantee a high operating security during data transmission. The possible data transmission acc. to ISO 11898 for max. 40m is 1 Mbit/s.

UNITRONIC® BUS CAN FD P is intended for high flexible application in power chains, or permanently moving machines, in dry and damp interiors and in harsh industrial environment.

Design




| | |
|--------------------------|--|
| Certification | UL / cUL Typ CMX according to UL 444 and CSA C22.2 No.214-02. |
| Conductor | bare copper, 0.25 mm ² (24 AWG), fine-wire stranded |
| Insulation | Foam-Skin PE, core Ø nom. 1.65 mm |
| Core identification code | pair 1: white and brown, pair 2: green and yellow (DIN 47100) |
| Stranding | 2 cores twisted to pair, 2 pairs stranded to bundle with two fillers non-woven tape |
| Screen | braid of tinned copper wires |
| Outer sheath | PUR, flame retardant, halogen free, violet similar to RAL 4001, Outer diameter: ca. 8.4 mm |

Electrical properties at 20°C

| | |
|--------------------------|---|
| Loop resistance | max. 159,8 Ω/km |
| Insulation resistance | min. 5 GΩxkm |
| Mutual capacitance | nom. 40 nF/km (at 800 Hz) |
| Characteristic impedance | 120 Ω ± 15% (at f ≥ 1 MHz) |
| Attenuation | 100 kHz: nom. 0.6 dB/100 m 1 MHz: nom. 1.5 dB/100 m 5 MHz: nom. 4.3 dB/100 m 10 MHz: nom. 8.1 dB/100 m 20 MHz: nom. 10.5 dB/100 m |
| Near-end cross-talk | min. 40 dB (at 20 MHz) |
| Velocity of propagation | nom. 76 % |
| Signal transit time | 4,4 ns/m |
| Transfer impedance | at 30 MHz max. 250 mΩ/m |
| Test voltage | conductor/conductor 1500 V conductor/screen 1000 V |

| | | |
|----------------------|-----------------------|-------------|
| Creator: TOST / PDC | Document: DB2170273EN | Page 1 of 2 |
| Released: ALTE / PDC | Version: 06 | |

| | | |
|---------------------------|---|---|
| 2170273 | DATA SHEET |  |
| valid from: 01.01.2019 | UNITRONIC® BUS CAN FD P 2x2x0,25 | |

Mechanical and thermal properties

| | |
|------------------------|---|
| Minimum bending radius | fixed use 6 x cable Ø flexible use 15 x cable Ø |
| Temperature range | moved - 30° C to + 70° C static - 40° C to + 80° C |
| Flammability | flame retardant acc. to IEC 60332-1-2/UL 1581 VW-1 |
| Halogen free | halogen free acc. to VDE 0472-815 |
| General requirements | This cable is conform to the EU-Directive 2011/65/EU (RoHS, Restriction of the use of certain hazardous substances). |

| | | |
|---|--------------------------------------|-------------|
| Creator: TOST / PDC Released: ALTE / PDC | Document: DB2170273EN Version: 06 | Page 2 of 2 |
|---|--------------------------------------|-------------|