

15331000	DATA SHEET	
Valid from: 08.12.2020	ÖLFLEX® TRAIN 331 600V	


Application

ÖLFLEX® TRAIN 331 are halogen-free, highly flame retardant cables for use in railway vehicles and buses. They are designed for fixed installation and for applications, where limited movement may occur. They are particularly used in areas, where human and animal life as well as valuable property are exposed to high risk of fire hazards. ÖLFLEX® TRAIN 331 are oil-, fuel-, acid- and alkali resistant acc. to EN 50264-3-1.

Application range:

railway vehicles and buses: connecting lamps, heating equipment, switchgear, terminal boxes and power supply

Design



Design	acc. to EN 50264-3-1, 600 V, M for cables $\geq 1 \text{ mm}^2$
Norm references	EN 50264-3-1. Code designation M M = extra low temperature, extra oil and fuel resistant
Classification	EN 45545-2: Hazard Level HL1, HL2, HL3 (only for cables $0.5 \text{ mm}^2 - 240 \text{ mm}^2$) NF F 16-101: only for black cables ($1 \text{ mm}^2 - 300 \text{ mm}^2$) and GNYE cables ($1 \text{ mm}^2 - 95 \text{ mm}^2$) Internal Category A1, A2, B External Category A1, A2, B Category C for flame propagation Category F0 for smoke
Conductor	fine wire strands of tinned copper acc. to IEC 60228 resp. EN 60228, Class 5
Core isolation	electron beam cross-linked polymer compound EI 109 acc. to EN 50264-1
Core identification	black, GN/YE, red, blue, grey, brown, green, yellow, orange, white, violet

Electrical properties

Nominal voltage	U_0 / U : 0.6/1 kV AC
Max. permissible operating voltage:	U_m : 1.2 kV AC V_0 : 0.9 kV DC
Test voltage	3.5 kV AC; 8.4 kV DC

Creator: HESC/PDC Released: ALTE/PDC	Document: DB15331000EN Version: 07	Page 1 of 3
---	---------------------------------------	-------------

We reserve all rights according to DIN ISO 16016.

PD 0019/05_04.18EN

15331000	DATA SHEET	
Valid from: 08.12.2020	ÖLFLEX® TRAIN 331 600V	

Mechanical and thermal properties

Min. bending radius	Cable diameter \leq 12.0 mm
	for cautions bending: 3 x outer diameter (one bend at end of core) fixed installation: 4 x outer diameter occasional flexing: 5 x outer diameter
	Cable diameter $>$ 12.0 mm
	for cautions bending: 4 x outer diameter (one bend at end of core) fixed installation: 5 x outer diameter occasional flexing: 6 x outer diameter
Temperature range	fixed installation: -45 °C up to +120°C max. conductor temp. (20.000h) up to +145°C max. conductor temp. (3.000h)
	occasional flexing: -35 °C up to +120°C max. conductor temp. (20.000h)
	- 50°C acc. to GOST 33326-2015 and GOST 20.57.406-81 (method 203-1 und 205-1)
Short circuit temperature	max. +200°C (5s)

Fire protection acc. to EN 50264-1 / EN 45545 (only for cables 0.5 mm² – 240 mm²):

Classification	EN 45545-2: Hazard Level HL1, HL2, HL3
Flammability	acc. to IEC 60332-1-2 resp. EN 60332-1-2
No flame propagation acc. to	\geq 12 mm: IEC 60332-3-24 resp. EN 60332-3-24 $>$ 6 mm and $<$ 12mm: IEC 60332-3-25 resp. EN 60332-3-25 \leq 6 mm: EN 50305
Smoke density	acc. to EN 50264-1, light transmission: min. 70% acc. to IEC 61034-2 resp. EN 61034-2
Halogen-free	acc. to IEC 60754-1 resp. EN 60754-1 (chlorine and bromine) acc. to EN 60684-2 (fluorine)
Corrosivity	acc. to EN 50264-1, pH \geq 4.3 and conductivity \leq 10 μ S/mm acc. to IEC 60754-2 resp. EN 60754-2
Toxicity	acc. to EN 50264-1 (\leq 3) acc. to EN 50305

Fire protection acc. to NF (only for black cables 1mm² - 300 mm² and GNYE cores 1 mm²– 95 mm²):

Classification	NF F 16-101: Internal Category A1, A2, B External Category A1, A2, B Category C for flame propagation Category F0 for smoke
Flammability	acc. to NF C 32-070, Category C1 and C2
Smoke density	acc. to NF X 10-702
Toxicity	acc. to NF X 70-100

Creator: HESC/PDC Released: ALTE/PDC	Document: DB15331000EN Version: 07	Page 2 of 3
---	---------------------------------------	-------------

15331000	DATA SHEET	
Valid from: 08.12.2020	ÖLFLEX® TRAIN 331 600V	

Fire protection acc. to NFPA 130:

Flammability FT4/IEEE1202 acc. to UL1685
Vertical-Tray Fire-Propagation

Smoke release acc. to UL 1685

Material properties

Ozone resistance acc. to EN 50264-3-1, method B
acc. to EN 50305

Mineral oil resistance acc. to EN 50264-3-1

Fuel resistance acc. to EN 50264-3-1

Acid and alkali resistance acc. to EN 50264-3-1

UV resistance acc. to EN 50525-1 are cables with black sheath suitable for a permanent outdoor use.

Tests acc. to EN 50264-3-1

EU Directives These cables are conform to the EU-Directives 2014/35/EC (Low Voltage Directive)

Environmental information These cables meet the substance-specific requirements of the EU Directive 2011/65/EU (RoHS).

Conductor cross section [mm ²]	Max. wire ø [mm]	Max. conductor resistance (20°C) [Ohm/km]	Conductor ø reference value [mm]	Core ø [mm]	Fire load reference value [kWh/m]	Weight [kg/km]
0.5	0.21	40.1	0.95	2.15 ±0.2	0.02	9
0.75	0.21	26.7	1.15	2.35 ±0.2	0.02	12
1	0.21	20.0	1.3	2.5 -0.1+0.3	0.02	15
1.5	0.26	13.7	1.6	3.0 -0.2+0.3	0.03	22
2.5	0.26	8.21	2.0	3.4 -0.2+0.3	0.04	33
4	0.31	5.09	2.7	4.1 ±0.3	0.05	49
6	0.31	3.39	3.2	4.6 ±0.3	0.06	70
10	0.41	1.95	4.2	5.6 ±0.3	0.07	112
16	0.41	1.24	5.2	6.6 -0.4+0.6	0.09	174
25	0.41	0.795	6.5	8.3 -0.4+0.6	0.15	273
35	0.41	0.565	7.7	9.5 -0.4+0.8	0.17	374
50	0.41	0.393	9.7	11.7 -0.4+0.7	0.23	531
70	0.51	0.277	11.4	13.6 -0.4+0.9	0.30	739
95	0.51	0.210	13.4	15.6 -0.4+0.7	0.34	988
120	0.51	0.164	15.0	17.4 -0.4+0.8	0.41	1243
150	0.51	0.132	17.0	19.8 -0.5+0.8	0.53	1558
185	0.51	0.108	18.5	21.7 -0.5+0.9	0.68	1927
240	0.51	0.0817	22.0	25.4 -0.6+0.6	0.82	2487
300	0.51	0.0654	23.2	26.8 -0.6+1.6	0.92	3085

Creator: HESC/PDC Released: ALTE/PDC	Document: DB15331000EN Version: 07	Page 3 of 3
---	---------------------------------------	-------------