DATA SHEET 2170345

valid from: 05.06.2023

UNITRONIC BUS DN THIN FD P 1x2x 24 AWG + 1x2x 22 AWG



Application

Performance:

Field of use: Field bus cable for DeviceNet applications based on CAN technology standardized in IEC/EN 62026-3. For

links between industrial devices such as sensors and actuators and higher-level devices such as PLCs and


PCs. Suitable for highly flexible applications in power chains and permanent moved machine parts.

Screened foiled twisted pair cable, having a nominal impedance of 120 Ω . Designed for transmission rates

of 125 Kbit/s up to 500 Kbit/s. For cable lengths up to 100 m. The cable consists of two wires for data

transmission and two wires for power supply (24 V DC).

Characteristics: flame retardant, no flame propagation, UV resistant, halogen free for use as trunk cable or as drop cable in DeviceNet networks Applications:



Design

Certification E224262 (UL) CL2X SUN RES acc. to UL 13

E236660 c(UL)us CMX 75°C acc. to UL 444 and CSA C22.2 No. 214

Conductor fine-wire stranded tinned copper data pair:

24/19 AWG

conductor diameter: nom. 0.63 mm

fine-wire stranded tinned copper power pair:

22/19 AWG

conductor diameter: nom. 0.8 mm

Insulation foam-skin polyolefine data pair:

core diameter: nom. 2.0 mm

polyolefine power pair:

core diameter: nom. 1.4 mm

Core identification code white/blue data pair: power pair: red/black

Stranding data cores twisted to pair data pair:

power cores stranded to pair power pair:

overall assembly: screened data pair and screened power pair stranded around

a central drain wire

Screen data pair: plastic laminated aluminum foil

power pair: plastic laminated aluminium foil

overall assembly: braid of tinned copper wires (coverage 80 % ± 5 %) drain wire: fine-wire stranded tinned copper (22/19 AWG)

non-woven tape Taping overall assembly:

Outer sheath overall assembly: **TPU**

violet, similar RAL 4001

outer diameter: $6.8 \text{ mm} \pm 0.3 \text{ mm}$

Electrical properties at 20 °C

max. $181.8 \,\Omega/km$ Conductor resistance data pair: loop resistance: power pair: loop resistance: max. 114.8 Ω/km

screen: DC resistance: nom. $10.5 \Omega/km$ ≥ 5 GΩ×km data pair: core/core: power pair: core/core: ≥ 200 MΩ×km

Mutual capacitance data pair: core/core: nom. 39.37 nF/km (1 kHz)

nom. 78.74 nF/km (1 kHz) core/screen:

Document: DB2170345EN Creator: KIOS / PDC

Page 1 of 2 Version: 05 Released: ALTE / PDC

Insulation resistance

2170345

DATA SHEET

valid from: 05.06.2023

UNITRONIC BUS DN THIN FD P 1x2x 24 AWG + 1x2x 22 AWG



Capacitance unbalance data pair: core/core: nom. 3937 pF/km (1 kHz)

Characteristic impedance data pair: 1MHz: 120 Ω ± 12 Ω

Attenuation data pair: 125 kHz: nom. 0.95 dB/100m (125 kHz)

500 kHz: nom. 1.64 dB/100m (500 KHz) 1 MHz: nom. 2.3 dB/100m (1 MHz)

Velocity of propagationdata pair:1 MHz:nom. 0.7 cSignal propagation timedata pair:1 MHz:nom. 480 ns/km

Maximum operating voltage complete cable: EN/IEC: 300 V (not for power applications)

Nominal voltage power pair: EN/IEC: 24 V DC
Rated voltage complete cable: UL/CSA: 300 V
Test voltage complete cable: core/core: 2000 V
core/screen: 2000 V

Mechanical and thermal properties

Minimum bending radius complete cable: fixed: $7.5 \times \text{outer diameter}$

continuous flexing: 15 × outer diameter

Temperature range complete cable: fixed: -40 °C up to +80 °C

continuous flexing: -30 °C up to +70 °C

UL/CSA: 75 °C

Flammability VW-1 acc. to UL 13 §27 resp. UL 444 §7.14.5

Halogen free amount of halogen acid gas acc. to. EN 60754-1 resp. IEC 60754-1

Weather and UV resistance SUN RES acc. to UL 13 §29

General requirements These cables are conform to the EU-Directive 2011/65/EU (RoHS, Restriction of the use of

certain hazardous substances) and the LV-Directive 2014/35/EU (Low voltage Directive).

Environmental information These cables meet the substance-specific requirements of the EU Directive 2011/65/EU (RoHS).

Creator: KIOS / PDC Document: DB2170345EN

Released: ALTE / PDC Version: 05