# DATA SHEET

valid from: 07.04.2021

2027503

# ÖLFLEX® CRANE 2ST



## **Application**

ÖLFLEX® CRANE 2ST are high-flexible PVC control cables with two steel-wire supporting elements and cold-flexible PVC jacket. They are also suitable for use in dry, damp or wet areas. They are suitable for outdoor use if the indicated temperature range is observed. They are largely resistant to acids, alkalis and certain oils at room temperature.

They are suitable for light torsion applications (max. ± 45 °/m). For simplified installation, the two external steel support elements can be easily detached.

Application range: Connection of movable control panels and consoles, self supporting shaft cable, high rack systems etc.; not applicable as lift cable.

#### Design

Design based on VDE 0250

Conductor extra fine wire strands of bare copper, acc. to IEC 60228 resp. EN 60228, class 6

Insulation PVC-compound TI2 acc. to EN 50363-3

Core identification code acc. to VDE 0293-1, with or without GN/YE ground conductor

black cores with white numbers acc. to EN 50334

Taping non-woven wrapping over core stranding

Supporting element Two steel supporting elements with a tensile strength of 1.410 N each

which are oppositely integrated into the outer sheath.

steel rope diameter: approx 1.25 mm

Outer sheath PVC special compound acc. to EN 50363-4-1

colour: black, similar RAL 9005

#### Electrical properties at 20 °C

Nominal voltage U<sub>0</sub>/ U: 300 / 500 V AC

Test voltage 2000 V AC

## Mechanical and thermal properties

Minimum bending radius flexing: 20 x outer diameter

Temperature range flexing: -15 °C up to +70 °C max. conductor temperature flammability flame retardant acc. to IEC 60332-1-2 resp. EN 60332-1-2

Tests acc. to IEC 60811 resp. EN 60811 and EN 50395

General requirements These cables are conform to the EU-Directive 2014/35/EU (Low Voltage Directive)

Environmental information These cables meet the substance-specific requirements of the EU Directive 2011/65/EU (RoHS).