



2170937	DATA SHEET	
valid from: 29.11.2019	ETHERLINE® SERVO DQ FD P Cat.5e 2X2X26/19 AWG + 1x2x22/19 AWG	

Application

ETHERLINE® SERVO DQ FD Cat.5e is a signal cable for use in SIEMENS® SINAMICS S120 drive systems, and is conform to the open DRIVE-CLiQ encoder interface. With its one pair for power supply and two data signal pairs for Cat. 5e data transmission, the cable is suitable for application in the industrial environments. With its conductor construction as well as additional fillers, the cable is designed for applications in power chains and on permanently moved machine parts in dry and damp areas. The data pairs comply with the requirements of IEC 61156-6.

Design




Certification	Insulation: UL AWM style 11602 (300 V, 80°C) acc. to UL 758; Jacket: UL AWM style 20978 (300 V, 80°C) acc. to UL 758; cRU AWM I/II A/B (FT1) acc. to CSA C22.2 No. 210-15 VW-1 according to UL 1581
Data pairs	2x2x26/19 AWG
Conductor	bare copper, fine-wire stranded
Insulation	solid polyethylene core Ø: 0.90 mm
Core identification code	green/yellow, blue/pink
Stranding	twisted to pairs with fillers
Power pair	1x2x22/19 AWG
Conductor	tinned copper, fine-wire stranded
Insulation	solid polyethylene core Ø: 1.05 mm
Core identification code	red, black
Stranding	twisted to a pair with fillers
Global assembly	data pairs and power pair stranded together with fillers
Wrapping	non-woven tape, overlapping
Screen	plastic laminated aluminum foil (metal surface outside, overlapping) <u>on top:</u> braid of tinned copper wires coverage 85 % ± 5 %
Separator	non-woven tape, overlapping
Outer sheath	PUR, halogen free and flame retardant outer Ø: 6.9 mm ± 0.2 mm green, RAL 6018

Electrical properties at 20°C

Loop resistance	data pairs (26/19 AWG):	max. 14.60 Ω/100 m
	power pair (22/19 AWG):	max. 5.94 Ω/100 m
Insulation resistance	min. 2 GΩxkm	
Mutual capacitance	1 kHz:	nom. 50 nF/km

Creator: KIOS / PDC	Document: DB2170488EN	Page 1 of 2
Released: ALTE / PDC	Version: 01	

2170937	DATA SHEET	
valid from: 29.11.2019	ETHERLINE® SERVO DQ FD P Cat.5e 2X2X26/19 AWG + 1x2x22/19 AWG	

Characteristic impedance	100 Ω acc. to IEC 61156-6	
	100 MHz:	100 Ω ± 15 Ω
Velocity of propagation	0.67 c	
Signal propagation time	max. 520 ns/100 m	
Delay skew	max. 20 ns/100 m	
Peak operating voltage	30 V	
Test voltage	conductor/conductor:	1500 V
	conductor/screen:	1000 V

Mechanical and thermal properties

Minimum bending radius	fixed installation: 6x cable Ø moved: 8x cable Ø
Temperature range	fixed installation: -40 bis +80 °C moved: -30 bis +70 °C
Flammability	flame retardant acc. to IEC 60332-1-2, VW-1 acc. to UL 1581, FT1 acc. to UL 1581
Halogen free	EN 50267-2-1, VDE 0472-815
Oil resistance	EN 50363-10-2
General requirements	This cable is conform to the EU-Directive 2011/65/EU (RoHS, Restriction of the use of certain hazardous substances).

Transmission properties

The transmission properties meet the Cat.5e requirements of IEC 61156-6.

Typical transmission properties:

f [MHz]	Attenuation [dB/100m]	NEXT [dB/100m]	ACR-F [dB/100m]	RL [dB/100m]
1	2.7	70.0	67.3	29
4	5.4	61.0	55.6	30
10	8.5	56.0	47.5	31
16	11.3	53.0	41.7	31
31,25	16.0	48.0	32.0	27
62,5	23.4	43.0	19.6	27
100	29.7	40.0	10.3	25

Creator: KIOS / PDC	Document: DB2170488EN	Page 2 of 2
Released: ALTE / PDC	Version: 01	