## 2170129

# DATA SHEET

valid from: 10.02.2020

UNITRONIC® LAN 200 SF/UTP Cat.5e Y Flex 4x2x26/7 AWG



#### **Application**

Flexible data cable for transmission of digital and analog signals up to 200 MHz. The cable is mainly designed for the use in the area of the workstation. According to TIA/EIA-568, ISO/IEC 11801 2nd edition, EN 50173, EN 50288-2-2, IEC 61156-6. For application in LANs like IEEE 802.3: 10Base-T, 100Base-T, 100Base-T; FDDI; ISDN; ATM.

#### Design

Conductor bare copper AWG 26/7, stranded wire

Insulation PE, ca. 0.96 mm outer Ø

Core identification code pair 1: white-blue/blue, pair 2: white-orange/orange,

pair 3: white-green/green, pair 4: white-brown/brown

Stranding cores stranded to pair,

4 pairs stranded to bundle

Screen plastic laminated aluminum foil

on top:

braid of copper wire, tinned wire ca. 0,10 mm

Outer sheath PVC

grey, similar to RAL 7035 outer Ø: ca. 5.8 mm

#### Electrical properties at 20°C

Characteristic impedance nom. 100  $\Omega$  acc. to IEC 61156-6

Velocity of propagation 0.67 c

Signal propagation time  $\leq 510 \text{ ns}/100 \text{ m}$ Delay  $\leq 25 \text{ ns}/100 \text{ m}$ 

Screening attenuation > 40 dB

Peak operating voltage 100 V (not for power purposes)

Test voltage Core/Core: 700 V Core/Screen: 700 V

### Mechanical and thermal properties

Minimum bending radius during installation: 8 x cable Ø

fixed: 4 x cable Ø

Temperature range during installation: 0° C up to +50° C

fixed: -20° C up to +70° C

Flammability flame retardant acc. to IEC 60332-1-2 resp. EN 60332-1-2

General requirements

These cables are conform to the EU-Directive 2011/65/EU (RoHS, Restriction of the use of

certain hazardous substances) and the LV-Directive 2014/35/EU (Low voltage Directive).

Environmental information These cables meet the substance-specific requirements of the EU Directive 2011/65/EU (RoHS).