


2171061	<b>DATA SHEET</b>	
Valid from: 17.09.2018	<b>IE-PNC-5-M12D-A-(L*)-P-2-22-FD-M12D-S</b>	

## Product description

Industrial Ethernet Patchcord, Profinet Type C, Cat.5, angled plug M12 on straight plug M12, D-coded, PUR, for drag chain



This datasheet is also valid for other lengths configurations. Other lengths configurations on request

## Product variations

Article number	Article description	Length (L*) [m]
2171061	IE-PNC-5-M12D-A-1-P-2-22-FD-M12D-S	1
2171062	IE-PNC-5-M12D-A-2-P-2-22-FD-M12D-S	2
2171063	IE-PNC-5-M12D-A-3-P-2-22-FD-M12D-S	3
2171064	IE-PNC-5-M12D-A-5-P-2-22-FD-M12D-S	5
2171065	IE-PNC-5-M12D-A-10-P-2-22-FD-M12D-S	10
2171066	IE-PNC-5-M12D-A-20-P-2-22-FD-M12D-S	20


## General properties, Patchcord

Outer diameter, cable	6.5 mm
Number of cores	4
Outer sheath	PUR
Outer sheath, color	green similar to RAL 6018
Mating cycles, M12 connector	100
Screening	SF/UTP

## General properties, cable

LAPP-Article number of cable	2170894
LAPP-Description of cable	ETHERLINE FD P FC Cat. 5
Conductor, outer diameter	ca. 0.75 mm
Conductor, material	tinned copper, fine-wire stranded
Insulation, outer diameter	ca. 1.5 mm
Insulation, material	PE
Core identification code	acc. to IEC 708-1: white, yellow, blue, orange
Stranding	star quad
Wrapping	plastic tape plastic laminated aluminum foil
Screening	on top: braid of copper wire tinned wire, coverage ca. 85%

Creator: MANA2/PDP	Document: DB2171061EN	Page 1 of 3
Released: IVSE1/PDP	Version: 06	

2171061	<b>DATA SHEET</b>	
Valid from: 17.09.2018	<b>IE-PNC-5-M12D-A-(L*)-P-2-22-FD-M12D-S</b>	

### Electrical properties, cable at 20 °C

Resistance (loop)	≤ 120 Ω/km
Insulation material, specific electrical resistance	≥ 0.5 GΩ*km
Characteristic impedance (1 MHz to 100 MHz)	100 Ω ± 15 Ω
Signal propagation time	< 5.3 ns/m
Test voltage (rms 50 Hz, 1 min.), core-core	700 V
Test voltage (rms 50 Hz, 1 min.), core-screening	700 V

### Mechanical and thermal properties, cable

Minimum bending radius, during laying	8 x cable diameter
Minimum bending radius, fixed installation	5 x cable diameter
Permissible temperature range, during laying	-20 °C to +60 °C
Permissible temperature range, fixed installation	-30 °C to +70 °C
Sunlight resistance	sunlight resistant acc. to UL 1581 Sec. 1200
Flame propagation	flame retardant acc. to UL 1581 (VW-1)
Halogen free	halogen free acc. to VDE 0472-815
General requirements	Dangerous and forbidden substance acc. to RoHS directive (2002/95/EG) are not allowed to the manufacturing

### General properties, M12 connector

Coding	D
Protection degree	IP67/IP69 locked connector
Rated voltage max.	250 V
Rated current at 40 °C	4 A
Ambient temperature	-30 °C to +90 °C
Insulation resistance	≥ 10 <sup>8</sup> Ω
Locking nut with vibration protection	Yes
Tightening torque	1.0 Nm

### Materials, M12 connector

Contacts, base material	CuZn
Contacts, surface	Au
Grip body	TPU
Locking nut, base material	CuZn


### Standards

Product standard, M12 connector	DIN EN 61076-2-101
---------------------------------	--------------------


### Approvals

UL-listed, E-File	E249137
-------------------	---------

Creator: MANA2/PDP Released: IVSE1/PDP	Document: DB2171061EN Version: 06	Page 2 of 3
---	--------------------------------------	-------------

2171061	<b>DATA SHEET</b>	
Valid from: 17.09.2018	<b>IE-PNC-5-M12D-A-(L*)-P-2-22-FD-M12D-S</b>	

## Drawings



### Application range

Automation, industrial machinery and plant engineering

### Note

Photographs are not true to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP Released: IVSE1/PDP	Document: DB2171061EN Version: 06	Page 3 of 3
---	--------------------------------------	-------------