2170322

DATA SHEET

valid from: 01.01.2019

UNITRONIC® BUS PB FD P FC 1x2x0,64




Application

UNITRONIC® BUS PB FD P FC 1x2x0,64 is a field bus cable with 150 Ω nominal impedance and a length-related transmission rate by 93,75 kBit/s to 12 MBit/s. The oil resistant product has excellent shielding properties and is suitable for highly flexible applications (drag chains and frequently moved machine parts).

Design

Insulation

Attenuation



Certification UL/CSA type CMX acc. to UL 444 and CSA C22.2 No. 214

Conductor stranded bare copper wire

19 x 0,140 mm, Ø approx. 0,67 mm foamed skin polyethylene (02YS),

Ø 2,55 mm (nominal value)

Core identification code red/greer

Stranding 2 cores stranded to pair

plastic tape (overlapping)

Inner sheath PVC, nature, outer Ø approx. 5,40mm

Screen aluminium laminated shield foil under braid, tinned coper wires, coverage 55 % ±5 %

Taping (optional) thin non-woven tape, longitudinally applied

Outer sheath PUR (TMPU),

violet (similar RAL 4001), outer \emptyset : 7,8 mm \pm 0,2 mm

Electrical properties at 20°C

Insulation resistance min. 5 G Ω xkm

Inductance nom. 1000 μ H/km (800 Hz) Characteristic impedance 270 Ω (±10%) (9,6 kHz)

185 Ω (±10%) (38,4 kHz) 150 Ω (±10%) (3-20) MHz max. 0,3 dB/100m (9,6 kHz) max. 0,4 dB/100m (38,4 kHz)

max. 0,9 dB/100m (200 kHz) max. 2,5 dB/100m (4 MHz) max. 4,9 dB/100m (16 MHz)

Near-end cross-talk nom. 0,75

 $\begin{array}{lll} \mbox{Signal transit time} & \mbox{nom. 450 ns/100m (3-20) MHz} \\ \mbox{Transfer impedance} & \mbox{max. 10 m} \mbox{Ω/m (up to 20,0 MHz)$} \\ \mbox{Peak operating voltage} & \mbox{250 V (not for power applications)} \\ \mbox{Test voltage} & \mbox{core/core: 3600 V DC (3 seconds)} \end{array}$

core/core: 3600 V DC (3 seconds)

Creator: TOST / PDC Document: DB2170322EN
Released: ALTE / PDC Version: 03
Page 1 of 2

2170322

DATA SHEET

valid from: 01.01.2019

UNITRONIC® BUS PB FD P FC 1x2x0,64



Mechanical and thermal properties

Minimum bending radius moved: $15 \times \text{cable } \emptyset$

Temperature range fixed installation: -40 °C up to +80 °C

moved: $-30^{\circ}\text{C up to } +70^{\circ}\text{C}$

Flammability acc. to UL 2556 Abs. 9.4 (VW-1)
Oil resistance acc. to UL 13 Sec. 40 (60°)

General requirements This cable is conform to the EU-Directive 2011/65/EU

(RoHS, Restriction of the use of certain hazardous substances).