2171286

DATA SHEET

Valid from: 17.09.2018

IE-PNC-5-RJ45-(L*)-P-2-22-FD-OE



Product description

Industrial Ethernet Patchcord, Profinet Type C, Cat.5, straight plug RJ45 on free conductor end, PUR, for drag chain



This datasheet is also valid for other lengths configurations. Other lengths configurations on request

Product variations

Article number	Article description	Length (L*) [m]
2171286	IE-PNC-5-RJ45-1-P-2-22-FD-OE	1
2171287	IE-PNC-5-RJ45-2-P-2-22-FD-OE	2
2171288	IE-PNC-5-RJ45-3-P-2-22-FD-OE	3
2171289	IE-PNC-5-RJ45-5-P-2-22-FD-OE	5
2171290	IE-PNC-5-RJ45-10-P-2-22-FD-0E	10
2171291	IE-PNC-5-RJ45-20-P-2-22-FD-OE	20

General properties, Patchcord

Outer diameter, cable 6.5 mm

Number of cores 4

Outer sheath PVC

Outer sheath, color green similar to RAL 6018

General properties, cable

LAPP-Article number of cable 2170894

LAPP-Description of cable ETHERLINE FD P FC Cat. 5

Conductor, outer diameter ca. 0.75 mm

Conductor, material tinned copper, fine-wire stranded

Insulation, outer diameter ca. 1.5 mm

Insulation, material PE

Core identification code acc. to IEC 708-1: white, yellow, blue, orange

Stranding star quad Wrapping plastic tape

Screening plastic laminated aluminum foil

on top: braid of copper wire tinned wire, coverage ca. 85%

2171286

DATA SHEET

Valid from: 17.09.2018

IE-PNC-5-RJ45-(L*)-P-2-22-FD-OE



Electrical properties, cable at 20°C

Resistance (loop) $\leq 120 \, \Omega/\text{km}$ Insulation material, specific electrical resistance $\geq 0.5 \, \text{G}\Omega^*\text{km}$ Characteristic impedance (1 MHz to 100 MHz) $100 \, \Omega \pm 15 \, \Omega$ Signal propagation time $< 5.34 \, \text{ns/m}$ Test voltage (rms 50 Hz, 1 min.), core-core $700 \, \text{V}$ Test voltage (rms 50 Hz, 1 min.), core-screening $700 \, \text{V}$

Mechanical and thermal properties, cable

Minimum bending radius, during laying 8 x cable diameter Minimum bending radius, fixed installation 8 x cable diameter Permissible temperature range, during laying -20 $^{\circ}$ C to +60 $^{\circ}$ C Permissible temperature range, fixed installation -30 $^{\circ}$ C to +70 $^{\circ}$ C

Flame propagation flame retardant acc. to UL 1581 (VW-1)
Halogen free halogen free acc. to VDE 0472-815

General requirements

Dangerous and forbidden substance acc. to RoHS

directive (2011/65/EG) are not allowed to the

manufacturing

General properties, RJ45 connector

Protection degree IP20
Rated voltage max. 50 V
Rated current at 40 °C 1 A

Ambient temperature -20 °C to +75 °C

Insulation resistance $\geq 10^8 \Omega$

Materials, RJ45 connector

Contacts, base material CuZn
Contacts, surface Au
Grip body TPU

Standards

Product standard, RJ45 connector DIN EN 60603-7-51

2171286


DATA SHEET


Valid from: 17.09.2018

IE-PNC-5-RJ45-(L*)-P-2-22-FD-OE





Drawings





Contact Configuration





Application range

Automation, industrial machinery and plant engineering

Note

Photographs are not true to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB2171286EN	Page 3 of 3
Released: IVSE1/PDP	Version: 02	