Valid from: 17.09.2018

AB-C5-M12FS-PG9-0,5



Description

- Sensor/Actuator flush-type socket, 5-pos., A-coded, M12
- Front/screw mounting with PG9 thread, with 0.5 m TPE litz wire, 5 x 0.34 mm²



General characteristics

Number of poles	5
Connection type	Fixed connection
Status indicator	No
Coding	A-standard
Degree of protection	IP 67
Inflammability class acc. to UL 94	VO
Ambient temperature (operation)	-25 to +90 °C (-13 to 194 °F) (cable, fixed installation)
	-25 to +85 °C (-13 to 185 °F) (connector)

Electrical properties

Nominal voltage U_N	60 V
Nominal current I _N	4 A
Surge voltage category	II
Pollution degree	3
Insulation resistance	20 m Ω^* km
Contact resistance	$3~{ m m}\Omega$

Mechanical properties

Connector

Contact, material	CuZn
Contact surface, material	Au
Contact carrier, material	PA66 GF
Knurl, material	Brass (nickel-plated)
Sealing, material	NBR

Line

Cable type	TPE litz wire
Conductor, material	Tin plated copper litz wires
Core insulation, material	PE
Conductor diameter including insulation	1.2 mm
Conductor cross section	0.34 mm ²
AWG signal line	22

Creator: MOKO2/PDP	Document: DB22260111EN	Dess 1 of 2
Released: IVSE1/PDP	Version: 03	Page 1 of 2
We reserve all rights according to DIN ISO 16016		





Valid from: 17.09.2018


AB-C5-M12FS-PG9-0,5




Technical drawing









Application range

Connection of enclosures and cabinets

Note

Photographs are not true to scale and do not represent detailed images of the respective products.

Creator: MOKO2/PDP Released: IVSE1/PDP	Document: DB22260111EN Version: 03	Page 2 of 2	
We reserve all rights according to DIN ISO 16016.			