Valid from: 17.09.2018

AB-C4-M12FS-PG9-0,5



Description

- Sensor/Actuator flush-type socket, 4-pos., A-coded, M12
- Front/screw mounting with PG9 thread, with 0.5 m TPE litz wire, 4 x 0.34 mm²



General characteristics

Number of poles	4
Connection type	Fixed connection
Status indicator	No
Coding	A-standard
Degree of protection	IP 67
Inflammability class acc. to UL 94	VO
Ambient temperature (operation)	-25 to +90 °C (-13 to 194 °F) (cable, fixed installation)
	-25 to +85 °C (-13 to 185 °F) (connector)

Electrical properties

 $\begin{array}{ll} \mbox{Nominal voltage } U_N & 250 \ V \\ \mbox{Nominal current } I_N & 4 \ A \\ \mbox{Surge voltage category} & II \\ \mbox{Pollution degree} & 3 \\ \mbox{Insulation resistance} & 20 \ m\Omega^* \mbox{km} \\ \mbox{Contact resistance} & 3 \ m\Omega \\ \end{array}$

Mechanical properties

Connector

Contact, material Contact surface, material Contact carrier, material Knurl, material Sealing, material

Line

Cable type	TPE litz wire
Conductor, material	Tin plated copper litz wires
Core insulation, material	PE
Conductor diameter including insulation	1.2 mm
Conductor cross section	0.34 mm ²
AWG signal line	22

Creator: MOKO2/PDP Released: IVSE1/PDP	Document: DB22260114EN Version: 03	Page 1 of 2		
Released. IVOL I/I DI				
We reserve all rights according to DIN ISO 16016.				
PD 0019/05_04.18EN				

CuZn

PA66 GF

Brass (nickel-plated)

Au


NBR

Valid from: 17.09.2018

AB-C4-M12FS-PG9-0,5



Technical drawing



Application range

Connection of enclosures and cabinets

Note

Photographs are not true to scale and do not represent detailed images of the respective products.

Creator: MOKO2/PDP Released: IVSE1/PDP	Document: DB22260114EN Version: 03	Page 2 of 2
We reserve all rights according to DIN ISO 16016.		