


2170474	DATA SHEET	
valid from: 09.08.2021	ETHERLINE® Cat. 7 Y 4x2x22/1 AWG	


Application

Field of use: Installation cable for cabling systems acc. to ISO/IEC 11801 and EN 50173. Meeting the transmission requirements of IEC 61156-5, Category 7 and EN 50288-4-1. Compliant to the "PROFINET Cabling and Interconnection Technology" guideline.

Performance: 4-pair, screened foiled twisted pair cable (S/FTP), having a nominal impedance of 100 Ω, supporting a bandwidth of 10 Gbit/s (e.g. 100BASE-T, 1000BASE-T, 2.5GBASE-T, 5GBASE-T, 10GBASE-T) over up to 100 m.

Characteristics: Flame retardant, no flame propagation, oil resistant

Applications: PROFINET, EtherCAT, EtherNet/IP, PoE (IEEE 802.3af), PoE+ (IEEE 802.3at), PPOE (IEEE 802.3bt) and others



Design

Conductor: solid bare copper
22/1 AWG

Insulation: polyolefin (foamed)
core diameter: nom. 1.50 mm

Core identification code: pair 1: white/blue, pair 2: white/orange, pair 3: white/green, pair 4: white/brown
(colored ring marking on the white cores is optional)

Stranding: 2 cores stranded to pair,
4 pairs stranded to bundle

Pair screen: plastic laminated aluminium foil (overlapping)


Screen: braid of tinned copper wires (coverage 85 % ± 5 %)

Outer sheath: PVC
green, similar RAL 6018
outer diameter: 8.70 mm (± 0.3 mm)

Electrical properties at 20 °C

Loop resistance	≤ 12.2 Ω/100 m	
Insulation resistance	≥ 5 GΩ×km	
Mutual capacitance	800 Hz:	42 nF/100 m
Coupling attenuation	30 MHz - 100 MHz:	≥ 80 dB
	100 MHz - 600 MHz:	≥ 80 - 20×log10(f / 100)
Characteristic impedance	100 MHz:	100 Ω acc. to IEC 61156-5
Velocity of propagation	100 MHz:	0.80 c
Signal propagation time	4 MHz - 600 MHz:	≤ 480 ns/100 m
Delay skew	4 MHz - 600 MHz:	≤ 20 ns/100 m
Maximum operating voltage	EN:	100 V (not for power applications)
Test voltage	core/core:	700 V
	core/screen:	700 V

Creator: KIOS / PDC	Document: DB2170474EN	Page 1 of 2
Released: ALTE / PDC	Version: 04	

2170474	DATA SHEET	
valid from: 09.08.2021	ETHERLINE® Cat. 7 Y 4x2x22/1 AWG	

Electrical transmission properties at 20°C

The transmission characteristics meet the requirements of the standards EN 50288-4-1 and IEC 61156-5 for category 7. The normative requirements for the transmission properties are shown in the following table:

f [MHz]		4	10	20	62,5	100	200	250	500	600
(max.) Attenuation [dB/100 m]		3,6	5,7	8,1	14,5	18,5	26,8	30,2	44,1	48,9
(min.) TCL [dB]		34	30	27	22	20	17	16	13	12,2
(min.) EL TCTL [dB/100 m]		23	15	9,0	—	—	—	—	—	—
(min.) NEXT [dB]		80	80	80	75,5	72,4	67,9	66,5	61,9	60,8
(min.) PS EL FEXT [dB/100 m]		77	71	65	55,1	51	45	43	37	35,4
(min.) ACR-F/EL FEXT [dB/100 m]		80	74	68	58,1	54	48	46	40	38,4
(min.) Return Loss [dB]		23	25	25	21,5	20,1	18	17,3	17,3	17,3

Mechanical and thermal properties

Minimum bending radius	fixed installation:	10 × outer diameter
Temperature range	fixed installation:	-30 °C up to +80 °C
Flammability	flame retardant acc. to IEC 60332-1-2 resp. EN 60332-1-2	
	no flame propagation acc. to IEC 60332-3-25 resp. EN 60332-3-25	

General requirements

This cable is conform to the EU-Directive 2011/65/EU (RoHS, Restriction of the use of certain hazardous substances) and the LV-Directive 2014/35/EU (Low voltage Directive).

Environmental information

These cables meet the substance-specific requirements of the EU Directive 2011/65/EU (RoHS).

Creator: KIOS / PDC	Document: DB2170474EN	Page 2 of 2
Released: ALTE / PDC	Version: 04	